


Outline Dimensions

JB1233-1



| CASE #. | A | B | C | D | E | F | G | H | J | K | L | M | WT, GRAM |
|----------|----------------|---------------|---------------|----------|----------------|----------------|----------------|----------------|----------------|----------------|-----------------|----------------|----------|
| JB1233-1 | .70 (17.78) | .32 (8.13) | .14 (3.56) | -- -- | .100 (2.54) | .125 (3.17) | .022 (0.56) | .060 (1.52) | .040 (1.02) | .360 (9.14) | .670 (17.02) | .175 (4.45) | 0.8 |

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Open style, Base material: Printed wiring laminate.
- Termination finish: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified