


Outline Dimensions



* OVERALL CONNECTOR DIMENSION
(CONNECTOR SHAPE MAY VARY)

MB1629 SERIES

2.92mm K-MALE (CONN-1)

2.92mm K-MALE (CONN-2)

CASE STYLE #	A		B	C	D	E	T		WEIGHT GRAMS
	FEET	METERS					INCH	MM	
MB1629-1.5	1.50	.46	.36 (9.14)	.312 (7.92)	.36 (9.14)	.312 (7.92)	+ .50/-0	+12.7/-0	58
MB1629-2	2.00	.61					+ .50/-0	+12.7/-0	69
MB1629-3.28	3.28	1.00					+ .79/-0	+20.0/-0	97
MB1629-4	4.00	1.22					+ .96/-0	+24.4/-0	113
MB1629-6.56	6.56	2.00					+1.57/-0	+40.0/-0	168

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. Phase Stable Armored Flexible Cable.