


Outline Dimensions



NA1922 SERIES

2.92mm MALE (CONN-1)

2.92mm RUGGED FEMALE (CONN-2)

CASE STYLE #	A		B	C	D	E	F	T		WEIGHT GRAMS
	FEET	METERS						INCH	MM	
NE1922-2.1	2.08	.63	.62 (15.75)	.312 (7.92)	.86 (21.84)	-	.750 (19.05)	+.50/-0	+12.7/-0	182.0
NE1922-3	3.00	.91						+.72/-0	+18.29/-0	210.0

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Note:

- VNA 26.5 and 40 GHz Coaxial Cable.