


Case Style

Outline Dimensions

UL

UL3030



UL3030 SERIES 2.4 MM MALE (CONN)

CASE STYLE #	A		B	C1	D	E1	F		T		WT. (GRAMS)
	INCH	MM					FL47U-AVM+ (UN-JACKETED)	FL47-AVM+ (JACKETED)	INCH	MM	
UL3030-6	6.00	157.40							.05	1.27	9.34
UL3030-12	12.00	304.80	.36	.315	.36	.315	.046±.004	.055±.004	.10	2.54	10.18
			[9.14]	[8.00]	[9.14]	[8.00]	[1.17±0.1]	[1.40±0.1]			

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2 Pl.±.03; 3 Pl. ±.015

Note:

1. 047 Flexible Coaxial Cable.
2. "A" Represents Length of Cable.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL-NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS