


Outline Dimensions

UU2046-2



CASE#	A	B	C	D	E	F	G	H	J	K	L
UU2046-2	3.10 (78.74)	3.28 (83.31)	.30 (7.62)	.150 (3.81)	2.800 (71.12)	1.64 (41.66)	.144 (3.66)	1.55 (39.37)	.13 (3.30)	.500 (12.70)	1.000 (25.40)

CASE#	M	N	WT, GRAMS
UU2046-2	--	.55 (13.97)	85

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS