


Outline Dimensions

UU2415



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
UU2415	4.46 (113.28)	5.75 (146.05)	.38 (9.65)	.13 (3.18)	4.200 (106.68)	.88 (22.35)	.125 (3.18)	2.23 (56.64)	.19 (4.83)	.500 (12.70)	.48 (12.19)	4.000 (101.60)

CASE#	N	WT. GRAMS
UU2415	--	800

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Blue Painting Pantone 286.
- Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/MICROWAVE COMPONENTS