

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92MM-MALE 1 RETURN LOSS (dB)	2.92MM-MALE 2 RETURN LOSS (dB)
100	0.11	25.0	42.4
200	0.11	27.6	47.3
300	0.11	30.5	39.9
400	0.22	29.2	37.4
500	0.15	35.0	45.9
600	0.18	27.2	35.0
700	0.17	49.4	39.0
800	0.25	28.9	33.7
900	0.20	31.8	31.2
1000	0.26	33.7	48.3
2000	0.36	33.9	28.4
3000	0.49	32.7	30.9
4000	0.58	35.1	31.8
5000	0.70	40.5	34.4
6000	0.77	38.3	37.8
7000	0.85	40.5	32.7
8000	0.89	31.3	32.3
9000	1.04	40.9	46.8
10000	1.08	27.5	23.0
11000	1.17	22.2	22.2
12000	1.24	27.5	28.5
13000	1.33	26.7	26.8
14000	1.44	27.1	28.9
15000	1.47	27.6	30.7
16000	1.53	26.8	27.0
17000	1.62	25.5	25.7
18000	1.66	35.5	26.9
19000	1.70	26.2	23.8
20000	1.76	32.3	35.8
21000	1.83	24.2	27.7
22000	1.91	21.2	21.7
23000	1.95	22.9	22.5
24000	2.03	27.6	23.8
25000	2.10	27.2	29.4
26000	2.17	22.2	23.6
27000	2.26	21.2	24.9
28000	2.26	20.5	21.3
29000	2.28	32.1	28.1
30000	2.37	34.1	28.1
31000	2.40	37.9	37.9
32000	2.47	25.7	38.9
33000	2.50	24.2	32.6
34000	2.64	20.7	23.4
35000	2.64	21.6	23.4
36000	2.72	30.0	34.4
37000	2.67	32.1	34.0
38000	2.81	26.6	36.9
39000	2.86	23.0	27.1
40000	2.96	23.5	28.7