

Hand-Flex Coaxial Cable, Right Angle SMA-M/SMA-F Bulkhead 086-18SBSMR+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE RETURN LOSS (dB)	SMA-FEMALE BULKHEAD RETURN LOSS (dB)
100.0	0.09	33.0	32.4
200.0	0.13	41.1	40.5
300.0	0.16	38.6	38.1
400.0	0.19	40.9	39.8
500.0	0.22	38.7	38.3
600.0	0.24	37.0	36.2
700.0	0.26	36.7	36.8
800.0	0.28	33.7	32.4
900.0	0.30	36.1	36.6
1000.0	0.32	32.1	31.4
1100.0	0.33	34.3	35.1
1250.0	0.36	32.4	31.7
1500.0	0.40	30.9	30.8
1750.0	0.43	28.7	29.4
2000.0	0.46	28.5	28.7
2250.0	0.49	28.6	30.3
2500.0	0.52	28.0	29.8
2750.0	0.55	27.9	29.8
3000.0	0.57	28.3	30.4
3250.0	0.60	26.9	29.0
3500.0	0.62	27.3	29.7
3750.0	0.64	27.7	30.3
4000.0	0.67	28.4	31.1
4250.0	0.69	29.0	33.1
4500.0	0.72	30.8	32.5
5000.0	0.76	33.3	30.7
5500.0	0.79	30.2	28.2
6000.0	0.83	30.4	29.0
6500.0	0.87	28.9	27.4
7000.0	0.91	27.7	26.2
7500.0	0.96	27.4	25.3
8000.0	0.99	30.6	27.7
8500.0	1.03	28.5	25.8
9000.0	1.05	26.5	27.7
9500.0	1.07	27.7	26.0
10000.0	1.10	34.3	28.2
10500.0	1.14	30.6	28.2
11000.0	1.16	30.8	27.6
11500.0	1.19	33.3	29.4
12000.0	1.22	32.0	30.0
12500.0	1.26	30.3	28.2
13000.0	1.29	29.4	27.7
13500.0	1.34	27.0	27.9
14000.0	1.37	26.5	27.4
14500.0	1.38	25.6	27.2
15000.0	1.42	24.3	26.8
15500.0	1.44	24.4	25.9
16000.0	1.47	25.6	27.5
16500.0	1.49	25.5	26.3
17000.0	1.52	23.8	24.7
17500.0	1.57	23.9	25.3
18000.0	1.69	19.3	19.9

