

SMA-Male to Right Angle SMA-Male

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE RETURN LOSS (dB)
10	0.04	45.6	45.3
50	0.08	38.9	38.9
100	0.11	38.6	38.6
140	0.12	40.0	39.6
220	0.16	60.2	57.5
260	0.18	45.5	45.5
300	0.20	42.0	41.7
340	0.20	42.1	41.8
380	0.22	46.1	44.4
460	0.24	51.0	47.7
500	0.26	46.6	40.7
550	0.27	46.8	38.5
600	0.28	52.2	40.4
650	0.29	55.8	48.4
700	0.30	47.6	47.2
750	0.32	46.9	40.2
800	0.33	51.8	38.5
850	0.33	56.0	40.2
900	0.35	45.6	44.9
950	0.35	42.9	45.6
1000	0.36	43.7	40.8
1200	0.40	44.8	42.7
1400	0.44	47.9	56.9
1500	0.46	47.1	40.1
1600	0.47	51.5	47.3
1800	0.50	60.9	41.7
2000	0.53	49.5	38.1
2400	0.58	43.9	43.9
2600	0.60	45.6	46.8
3000	0.66	59.0	45.6
3400	0.68	39.9	38.5
3600	0.71	40.1	39.6
4000	0.76	38.0	38.8
4400	0.77	45.0	51.3
4600	0.80	46.4	52.4
5000	0.83	37.7	36.4
5400	0.87	37.4	38.3
5600	0.91	47.8	56.5
6000	0.92	37.2	37.3
6400	0.96	36.7	35.0
6600	1.00	31.2	30.9
7000	1.02	30.7	32.7
7400	1.05	27.6	27.7
7600	1.05	28.6	27.8
8000	1.06	35.1	31.7
8400	1.13	28.0	29.5
8600	1.21	24.8	25.5
9000	1.21	27.6	26.5
9200	1.21	32.7	29.6
9400	1.23	33.1	30.2
9600	1.25	30.7	32.2
9800	1.27	27.9	30.5
10000	1.31	24.7	26.0
11600	1.35	26.2	26.5
12000	1.37	26.6	26.7
12400	1.34	29.0	30.4
12800	1.39	40.8	40.4
13600	1.61	21.8	21.8
14000	1.62	27.3	27.3
14400	1.61	45.3	38.3
14800	1.63	27.6	27.9
15600	1.67	24.6	25.3
16000	1.65	31.1	48.8
16400	1.69	25.2	27.1
17600	1.78	27.9	33.0
18000	1.79	24.7	25.7