

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
10.0	0.01	56.17	55.67
50.0	0.03	48.57	48.57
100.0	0.04	46.27	46.98
200.0	0.06	45.29	44.67
300.0	0.07	45.03	44.65
400.0	0.08	48.06	45.98
500.0	0.10	54.55	49.81
600.0	0.10	58.05	71.66
700.0	0.11	50.66	51.65
800.0	0.12	45.91	45.84
900.0	0.13	45.95	43.32
1000.0	0.13	50.49	44.09
1100.0	0.14	62.02	48.45
1250.0	0.15	44.20	49.90
1500.0	0.17	42.12	40.71
1750.0	0.18	64.74	45.20
2000.0	0.19	43.49	46.09
2001.0	0.19	43.51	46.11
2250.0	0.21	45.50	38.54
2500.0	0.22	44.65	48.24
2750.0	0.23	40.60	37.08
3000.0	0.24	51.92	40.07
3250.0	0.25	37.80	37.67
3500.0	0.26	39.45	33.11
3750.0	0.27	42.14	42.33
4000.0	0.28	38.04	33.36
4250.0	0.28	48.36	35.57
4500.0	0.30	37.36	33.24
5000.0	0.31	42.63	36.03
5500.0	0.34	40.96	32.52
6000.0	0.34	44.36	31.77
6500.0	0.36	33.77	28.45
7000.0	0.36	30.64	26.95
7500.0	0.43	28.95	26.78
8000.0	0.42	29.89	29.00
8500.0	0.43	45.56	32.67
9000.0	0.44	32.75	26.24
9500.0	0.48	28.67	24.25
10000.0	0.49	22.66	20.12
10500.0	0.51	24.63	22.44
11000.0	0.54	26.04	25.77
11500.0	0.60	32.45	24.86
12000.0	0.56	25.02	19.59
12500.0	0.53	24.40	19.66
13000.0	0.56	23.12	20.03
13500.0	0.55	31.26	25.49
14000.0	0.58	25.90	30.04
14500.0	0.59	22.61	20.93
15000.0	0.63	21.34	19.21
15500.0	0.66	21.18	18.12
16000.0	0.61	28.14	25.11
16500.0	0.62	31.31	28.09
17000.0	0.62	26.24	24.73
17500.0	0.63	25.57	20.65
18000.0	0.59	28.62	21.38



ISO 9001 ISO 14001 AS 9100 CERTIFIED

