

Hand-Flex Coaxial Cable, SMA-M/N-M

141-10SMNM+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
100.0	0.02	39.3	39.0
200.0	0.03	37.3	36.6
300.0	0.05	39.6	38.7
500.0	0.06	43.3	42.4
600.0	0.07	36.3	35.8
800.0	0.07	45.0	45.4
900.0	0.08	45.2	46.5
1000.0	0.07	36.3	36.2
1200.0	0.10	39.0	39.4
1400.0	0.10	39.0	38.4
1600.0	0.12	36.0	36.8
1800.0	0.12	40.0	40.8
2000.0	0.13	33.9	34.1
2200.0	0.12	38.8	41.2
2400.0	0.12	37.1	37.0
2600.0	0.12	37.1	42.1
2800.0	0.14	35.9	36.5
3000.0	0.14	37.1	40.9
3500.0	0.14	36.9	40.3
4000.0	0.16	41.7	42.2
4500.0	0.17	40.8	40.9
5000.0	0.19	46.5	43.3
5500.0	0.14	38.0	37.2
6000.0	0.18	33.5	31.9
6500.0	0.17	32.5	32.1
7000.0	0.19	32.7	32.8
7500.0	0.22	30.0	31.4
8000.0	0.17	30.0	30.1
8500.0	0.22	28.8	25.4
9000.0	0.26	30.5	26.9
9500.0	0.31	31.0	24.2
10000.0	0.20	26.4	29.7
10500.0	0.19	28.2	27.1
11000.0	0.18	29.1	27.3
11500.0	0.35	29.4	28.4
12000.0	0.29	28.8	29.1
12500.0	0.39	25.3	27.8
13000.0	0.29	24.8	28.7
13500.0	0.27	24.7	35.0
14000.0	0.38	24.1	30.1
14500.0	0.34	22.6	24.9
15000.0	0.36	21.4	26.7
15500.0	0.41	22.2	23.8
16000.0	0.38	24.1	27.2
16500.0	0.41	23.1	27.4
18000.0	0.41	25.3	28.2