

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.03	49.1	45.3
200.0	0.04	45.1	49.9
300.0	0.06	47.1	48.5
400.0	0.07	47.8	50.0
500.0	0.08	49.0	50.4
600.0	0.09	49.1	50.0
700.0	0.11	49.0	51.7
800.0	0.11	49.8	51.4
900.0	0.11	50.1	50.1
1000.0	0.13	49.6	50.0
1200.0	0.14	49.9	47.5
1400.0	0.15	48.2	46.7
1600.0	0.17	48.7	45.7
1800.0	0.17	45.1	43.8
2000.0	0.18	42.5	42.1
2200.0	0.19	40.8	42.1
2400.0	0.19	40.3	42.2
2600.0	0.21	39.3	41.2
2800.0	0.22	39.4	40.6
3000.0	0.23	38.7	39.9
3500.0	0.25	38.0	38.7
4000.0	0.28	37.3	39.6
4500.0	0.30	37.7	39.6
5000.0	0.32	37.1	39.6
5500.0	0.32	35.9	37.9
6000.0	0.34	33.5	34.7
6500.0	0.35	34.4	35.7
7000.0	0.38	32.9	34.4
7500.0	0.37	33.0	33.9
8000.0	0.40	33.5	33.8
8500.0	0.42	33.4	33.3
9000.0	0.44	32.8	33.8
9500.0	0.45	32.6	33.6
10000.0	0.46	30.9	31.7
10500.0	0.46	30.7	32.1
11000.0	0.46	31.5	32.2
11500.0	0.47	31.4	32.9
12000.0	0.45	32.2	33.2
12500.0	0.51	32.1	32.7
13000.0	0.51	31.7	32.8
13500.0	0.52	30.8	31.2
14000.0	0.54	30.1	30.6
14500.0	0.55	29.4	29.7
15000.0	0.57	28.4	29.0
15500.0	0.54	28.4	29.4
16000.0	0.59	27.2	28.0
16500.0	0.62	26.9	28.2
17000.0	0.64	26.3	27.4
17500.0	0.63	26.1	27.6
18000.0	0.65	23.4	30.6