

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
10.0	0.02	38.57	39.05
50.0	0.04	44.77	45.16
100.0	0.06	39.49	39.52
200.0	0.08	45.69	45.44
300.0	0.10	41.20	40.41
400.0	0.11	39.52	38.51
500.0	0.13	47.93	45.76
600.0	0.14	37.15	35.98
700.0	0.15	56.63	54.72
800.0	0.16	37.15	36.13
900.0	0.18	42.82	41.50
1000.0	0.19	39.01	38.09
1100.0	0.20	38.18	37.73
1250.0	0.21	37.79	37.51
1500.0	0.23	36.11	36.77
1750.0	0.25	35.99	37.27
2000.0	0.27	36.88	37.52
2001.0	0.27	36.90	37.55
2250.0	0.29	38.86	37.85
2500.0	0.31	38.26	35.88
2750.0	0.32	41.49	38.04
3000.0	0.34	41.30	39.35
3250.0	0.36	42.39	42.93
3500.0	0.38	42.17	46.04
3750.0	0.39	46.05	44.48
4000.0	0.41	51.35	40.55
4250.0	0.41	51.67	41.55
4500.0	0.43	41.99	39.57
5000.0	0.46	37.74	35.85
5500.0	0.50	34.81	35.61
6000.0	0.54	31.45	33.10
6500.0	0.57	30.26	29.77
7000.0	0.59	33.42	32.67
7500.0	0.60	37.68	36.69
8000.0	0.63	39.08	36.56
8500.0	0.66	38.58	48.36
9000.0	0.68	32.92	33.02
9500.0	0.69	35.44	33.77
10000.0	0.71	30.92	30.18
10500.0	0.76	35.70	38.47
11000.0	0.79	54.61	38.31
11500.0	0.81	34.73	34.40
12000.0	0.80	35.25	35.04
12500.0	0.83	34.80	32.34
13000.0	0.87	34.31	40.07
13500.0	0.91	32.80	36.81
14000.0	0.93	39.41	32.34
14500.0	0.96	46.61	37.32
15000.0	0.98	30.33	34.61
15500.0	0.93	34.48	34.74
16000.0	0.98	26.51	27.43
16500.0	1.08	28.08	34.05
17000.0	1.15	28.47	33.96
17500.0	1.11	33.66	37.81
18000.0	1.10	37.86	30.48