

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
10	0.07	43.1	42.0
50	0.08	33.6	33.2
100	0.11	49.0	49.8
200	0.17	46.1	46.0
300	0.21	42.9	43.5
400	0.24	39.7	40.1
500	0.28	39.0	39.5
1000	0.41	34.7	35.0
1500	0.51	36.7	38.2
2000	0.60	41.6	50.1
2500	0.67	39.5	40.4
3000	0.75	35.9	35.8
3500	0.82	35.9	35.8
4000	0.89	37.2	44.5
4500	0.95	33.7	35.4
5000	1.01	34.0	34.6
5500	1.07	32.8	34.2
6000	1.12	33.1	36.5
6500	1.18	30.5	30.9
7000	1.23	37.0	40.8
7500	1.27	50.2	37.0
8000	1.32	31.7	34.9
8500	1.37	31.3	32.6
9000	1.42	32.3	33.5
9500	1.47	31.4	34.6
10000	1.52	31.4	33.9
10500	1.57	27.8	29.1
11000	1.61	35.4	34.9
11500	1.65	32.1	33.9
12000	1.70	29.5	30.0
12500	1.75	25.1	26.3
13000	1.78	35.6	38.5
13500	1.82	32.6	32.8
14000	1.87	27.6	29.5
14500	1.91	30.2	28.9
15000	1.95	31.2	34.7
15500	1.99	51.6	36.2
16000	2.02	32.5	34.4
16500	2.06	40.3	36.9
17000	2.11	38.6	42.9
17500	2.16	24.8	25.2
18000	2.20	26.1	25.4