

# Fixed Attenuator

# BW-V20-1W54+

## Typical Performance Data

| FREQUENCY<br>(GHz) | ATTENUATION<br>(dB) | VSWR<br>(:1) |
|--------------------|---------------------|--------------|
| 0.01               | 19.74               | 1.03         |
| 1.0                | 19.76               | 1.03         |
| 5.0                | 19.83               | 1.03         |
| 10                 | 19.85               | 1.04         |
| 12                 | 19.85               | 1.05         |
| 14                 | 19.84               | 1.06         |
| 18                 | 19.82               | 1.08         |
| 19                 | 19.83               | 1.08         |
| 19                 | 19.83               | 1.09         |
| 19                 | 19.83               | 1.09         |
| 20                 | 19.83               | 1.09         |
| 20                 | 19.82               | 1.10         |
| 20                 | 19.82               | 1.10         |
| 22                 | 19.82               | 1.13         |
| 24                 | 19.82               | 1.15         |
| 26                 | 19.84               | 1.16         |
| 28                 | 19.81               | 1.16         |
| 30                 | 19.78               | 1.15         |
| 32                 | 19.77               | 1.18         |
| 34                 | 19.75               | 1.17         |
| 36                 | 19.74               | 1.17         |
| 38                 | 19.74               | 1.18         |
| 40                 | 19.75               | 1.15         |
| 42                 | 19.72               | 1.10         |
| 44                 | 19.71               | 1.07         |
| 46                 | 19.73               | 1.09         |
| 48                 | 19.77               | 1.11         |
| 50                 | 19.84               | 1.13         |

