

Test Cable, SMA-Male/N-Male

CBL-10FT-SMNM+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
100.0	0.32	49.80	48.18
733.3	0.93	32.84	32.61
1366.7	1.31	30.62	30.05
2000.0	1.61	30.23	29.62
2000.3	1.61	30.38	29.72
2000.7	1.61	30.55	29.84
2001.0	1.61	30.72	29.96
3334.0	2.15	43.50	31.50
4667.0	2.61	29.65	27.61
6000.0	3.00	29.13	41.75
6000.3	2.99	29.10	42.04
6000.7	3.00	29.02	42.59
6001.0	3.00	28.97	43.28
8000.7	3.59	34.97	33.78
10000.3	4.08	27.48	28.45
12000.0	4.52	25.09	23.54
12000.3	4.52	25.11	23.61
12000.7	4.52	25.12	23.66
12001.0	4.52	25.15	23.76
12858.0	4.83	24.26	24.09
13715.0	5.12	32.19	32.33
14572.0	5.25	30.55	27.63
15429.0	5.40	28.27	24.74
16286.0	5.64	30.00	30.24
17143.0	5.92	28.65	25.57
18000.0	6.01	23.28	35.08