

Test Cable, SMA-Male/SMA-Male

CBL-1FT-SMSM+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
100.0	0.05	46.11	44.56
416.7	0.09	40.53	43.13
733.3	0.12	32.58	33.38
1050.0	0.15	28.32	29.21
1366.7	0.17	27.80	28.87
1683.3	0.18	28.75	31.29
2000.0	0.20	28.97	32.84
2666.7	0.23	28.84	27.72
3333.3	0.26	27.63	25.70
4000.0	0.29	27.42	26.69
4666.7	0.32	26.95	30.46
5333.3	0.34	28.83	36.29
6000.0	0.37	35.24	41.62
7000.0	0.39	29.58	30.48
8000.0	0.40	23.22	25.81
9000.0	0.43	21.47	23.97
10000.0	0.47	23.07	24.43
11000.0	0.53	27.96	29.37
12000.0	0.58	40.34	32.69
12857.1	0.57	25.86	30.21
13714.3	0.60	33.35	28.39
14571.4	0.64	29.94	29.54
15428.6	0.66	27.96	24.53
16285.7	0.69	31.25	25.56
17142.9	0.71	27.25	23.46
18000.0	0.74	36.72	26.56