

Test Cable, N-Male/N-Male

CBL-5FT-NMNM+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
0.3	0.02	58.38	55.00
1.0	0.02	52.55	51.43
10	0.06	42.13	41.88
100	0.17	44.97	46.75
500	0.42	27.16	27.21
750	0.51	52.52	39.50
1000	0.62	25.19	25.32
1250	0.68	38.59	38.97
1500	0.75	27.51	27.46
1750	0.81	37.44	47.65
2000	0.88	30.27	30.04
2250	0.94	42.86	42.48
2500	0.99	41.62	38.44
2750	1.04	36.94	33.27
3000	1.10	48.79	46.98
3500	1.20	40.77	36.06
4000	1.29	33.10	31.58
4500	1.39	31.49	30.62
5000	1.48	30.13	28.32
5500	1.57	27.38	27.07
6000	1.64	29.67	27.68
6500	1.72	30.47	30.30
7000	1.80	48.90	36.34
7500	1.88	33.65	33.96
8000	1.97	28.98	27.02
8500	2.03	30.38	28.91
9000	2.10	33.94	33.82
9500	2.18	32.61	37.74
10000	2.24	30.63	37.29
11000	2.41	29.20	37.69
12000	2.52	27.14	30.36
13000	2.64	25.41	30.97
14000	2.86	23.82	22.86
15000	2.89	29.45	27.95
16000	3.15	25.71	27.09
17000	3.22	24.66	27.55
18000	3.38	30.75	34.74