

Test Cable, SMA-Male/SMA-Male

CBL-6FT-SMSM+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
50	0.16	53.78	53.72
100	0.22	52.32	48.58
300	0.40	40.23	41.48
500	0.48	49.60	46.27
700	0.60	34.48	34.93
900	0.68	40.11	41.32
1000	0.72	33.08	33.66
1300	0.83	31.76	32.19
1500	0.89	42.03	42.20
1700	0.95	30.89	30.90
1900	1.02	33.37	33.09
2000	1.04	29.90	29.34
2300	1.13	29.15	28.93
2500	1.17	37.22	48.47
2700	1.23	30.22	30.44
2900	1.28	32.04	32.45
3000	1.31	29.90	30.72
3500	1.41	41.29	38.47
4000	1.53	33.97	32.25
4500	1.63	43.55	47.03
5000	1.74	36.35	33.91
5500	1.83	44.40	38.48
6000	1.93	33.76	34.36
6500	2.02	41.68	37.09
7000	2.09	32.69	36.35
7500	2.20	29.51	29.30
8000	2.32	35.63	42.04
8500	2.42	26.43	29.75
9000	2.49	31.97	37.17
9500	2.55	28.88	31.70
10000	2.63	27.58	29.84
11000	2.73	30.36	29.90
12000	2.91	31.65	29.02
13000	3.03	26.00	28.61
14000	3.18	27.35	40.66
15000	3.31	23.81	33.96
16000	3.47	20.27	25.81
17000	3.59	22.14	27.47
18000	3.73	22.79	32.29