

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm-MALE 1 RETURN LOSS (dB)	2.92mm-MALE 2 RETURN LOSS (dB)
100	0.38	42.0	39.8
1000	1.21	42.0	40.3
2000	1.71	38.2	38.3
3000	2.09	33.5	35.4
4000	2.43	37.6	36.1
5000	2.73	33.4	33.4
6000	3.01	32.9	30.9
7000	3.27	27.2	25.8
8000	3.50	25.4	25.2
9000	3.72	28.7	27.9
10000	3.93	32.0	29.9
11000	4.13	33.0	29.7
12000	4.34	26.4	26.5
13000	4.53	24.8	22.4
14000	4.72	23.9	23.8
15000	4.88	29.0	24.6
16000	5.05	33.9	28.6
17000	5.23	26.6	28.3
18000	5.40	31.2	27.2
19000	5.57	28.4	26.0
20000	5.74	24.2	23.1
21000	5.89	24.6	23.2
22000	6.03	28.2	25.4
23000	6.17	30.9	32.0
24000	6.37	34.8	26.2
25000	6.55	37.9	22.4
26000	6.70	25.2	23.6
27000	6.84	26.9	23.2
28000	7.01	23.4	20.3
29000	7.15	24.1	21.5
30000	7.28	25.3	21.4
31000	7.43	28.4	22.2
32000	7.57	24.6	21.6
33000	7.73	21.5	19.4
34000	7.86	24.0	20.6
35000	7.98	24.0	20.8
36000	8.11	26.4	21.2
37000	8.25	27.0	22.4
38000	8.38	29.0	23.3
39000	8.52	26.7	21.0
40000	8.66	26.5	20.4