

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	SSMP-FEMALE RETURN LOSS (dB)	2.92mm-MALE RETURN LOSS (dB)
100	0.17	37.11	37.33
200	0.23	39.90	37.89
300	0.27	39.90	38.51
500	0.35	40.96	39.16
600	0.38	35.56	37.46
800	0.43	37.46	34.47
1000	0.48	32.70	34.00
2500	0.70	32.17	28.90
4000	0.87	37.08	28.97
5500	1.01	31.34	28.52
7000	1.14	29.49	27.78
8500	1.25	30.26	28.51
10000	1.35	30.30	31.35
11500	1.45	27.10	27.65
13000	1.55	24.37	23.61
14500	1.63	25.67	25.75
16000	1.70	33.06	35.21
17500	1.78	34.55	27.70
19000	1.86	33.63	26.91
20500	1.93	31.14	29.55
22000	2.01	33.41	32.23
23500	2.08	24.71	28.30
25000	2.17	22.94	22.89
26500	2.25	26.96	22.87
28000	2.31	38.42	26.29
29500	2.39	33.28	24.52
31000	2.50	26.18	20.66
32500	2.61	21.72	19.25
34000	2.62	24.27	23.44
35500	2.67	25.41	23.62
37000	2.70	34.70	25.15
38500	2.74	37.30	37.42
40000	2.79	23.85	37.13