

Test Cable, SMA-Male/SMA-Male

FLC-6FT-SMSM+

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 VSWR (:1)	SMA-MALE 2 VSWR (:1)
0.1	0.25	1.01	1.02
0.5	0.50	1.03	1.03
1.0	0.72	1.04	1.05
1.5	0.89	1.06	1.06
2.0	1.04	1.06	1.07
2.5	1.19	1.07	1.07
3.0	1.31	1.06	1.07
3.5	1.42	1.05	1.05
4.0	1.52	1.04	1.04
4.5	1.61	1.03	1.03
5.0	1.71	1.03	1.04
5.5	1.81	1.04	1.04
6.0	1.89	1.04	1.05
6.5	1.98	1.06	1.06
7.0	2.08	1.07	1.07
7.5	2.18	1.09	1.09
8.0	2.26	1.10	1.09
8.5	2.31	1.11	1.11
9.0	2.39	1.12	1.11
9.5	2.46	1.13	1.13
10.0	2.47	1.13	1.13
10.5	2.55	1.12	1.13
11.0	2.65	1.12	1.12
11.5	2.67	1.12	1.12
12.0	2.73	1.11	1.12
12.5	2.85	1.12	1.10
13.0	2.92	1.12	1.10
13.5	2.97	1.10	1.09
14.0	3.03	1.08	1.08
14.5	3.16	1.08	1.07
15.0	3.21	1.08	1.08
15.5	3.24	1.10	1.09
16.0	3.37	1.09	1.13
16.5	3.45	1.14	1.14
17.0	3.45	1.17	1.17
17.5	3.56	1.21	1.17
18.0	3.73	1.23	1.18
18.5	3.75	1.26	1.19
19.0	3.82	1.28	1.19
19.5	3.91	1.28	1.20
20.0	3.98	1.30	1.19
20.5	4.00	1.27	1.17
21.0	3.91	1.27	1.17
21.5	3.92	1.25	1.16
22.0	4.00	1.19	1.17
22.5	4.01	1.16	1.15
23.0	3.99	1.15	1.16
23.5	4.19	1.15	1.14
24.0	4.35	1.13	1.14
24.5	4.29	1.12	1.12
25.0	4.33	1.10	1.12
25.5	4.43	1.13	1.10
26.0	4.50	1.13	1.16

