

FREQ.	INSERTION LOSS RF - RF&DC	ISOLATION RF&DC - DC	VSWR RF&DC
(MHz)	(dB)	(dB)	(:1)
1000	2.06	21.78	2.63
1250	1.27	25.46	1.95
1500	0.93	28.70	1.62
1750	0.77	31.61	1.45
2000	0.69	34.27	1.35
2250	0.65	36.76	1.31
2500	0.63	39.09	1.30
2750	0.64	41.33	1.32
3000	0.65	43.46	1.35
3250	0.68	45.48	1.38
3500	0.70	47.37	1.41
3750	0.73	49.20	1.43
4000	0.75	50.87	1.44
4250	0.77	52.54	1.45
4500	0.78	53.97	1.43
4750	0.78	55.25	1.41
5000	0.77	55.94	1.37
5250	0.77	55.73	1.32
5500	0.76	54.67	1.27
5750	0.75	52.84	1.23
6000	0.74	51.22	1.18
6250	0.73	50.47	1.14
6500	0.72	50.83	1.12
6750	0.71	51.89	1.10
7000	0.71	52.84	1.09
7250	0.71	53.66	1.10
7500	0.71	54.09	1.11
7750	0.72	54.20	1.13
8000	0.73	54.07	1.16
8250	0.75	53.72	1.20
8500	0.78	53.36	1.23
8750	0.80	52.79	1.26
9000	0.83	52.12	1.28
9250	0.85	51.50	1.29
9500	0.87	50.84	1.30
9750	0.88	50.14	1.30
10000	0.89	49.37	1.29
10500	0.90	47.91	1.25
11000	0.90	46.64	1.20
11500	0.90	46.50	1.15
12000	0.88	47.70	1.11
12500	0.84	48.31	1.07
13000	0.79	48.23	1.04
13500	0.72	47.79	1.01
14000	0.65	47.33	1.03
14500	0.59	46.93	1.09
15000	0.55	46.40	1.15
15500	0.53	46.08	1.20
16000	0.51	46.04	1.23
16500	0.50	46.25	1.24
17000	0.49	46.64	1.25
17500	0.49	47.11	1.25
18000	0.52	47.58	1.29
18500	0.60	47.98	1.38
19000	0.74	48.37	1.51
19500	0.93	48.61	1.70
20000	1.16	49.09	1.91
20500	1.40	49.67	2.11
21000	1.60	50.26	2.25