

## Typical Performance Data

CARRIER FREQ.	CONVERSION LOSS	SIDE BAND REJECTION		CARRIER REJECTION		3rd HARMONIC SUPPRESSION		5th HARMONIC SUPPRESSION		DC OFFSET
		LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	
(MHz)	(dB)									(mV)
20.00	5.91	43.34	42.73	55.61	54.19	62.14	49.79	67.81	71.33	-0.21
20.16	5.92	43.32	42.65	55.18	54.49	62.28	49.76	67.35	71.99	-0.21
20.32	5.93	43.18	42.53	55.38	54.26	62.25	49.79	67.92	71.76	-0.21
20.47	5.92	42.68	43.11	55.35	55.03	62.01	50.37	67.65	72.60	-0.21
20.63	5.89	42.65	42.89	55.38	55.12	61.88	50.49	67.34	72.25	-0.21
20.79	5.89	42.31	42.86	54.99	54.89	61.93	50.56	67.59	71.96	-0.21
20.95	5.92	42.29	42.85	55.08	54.92	61.68	50.58	67.68	72.38	-0.21
21.11	5.90	42.48	42.85	55.15	54.91	61.45	50.61	67.65	72.48	-0.21
21.26	5.90	42.41	42.78	55.28	54.78	61.58	50.68	67.48	72.48	-0.21
21.42	5.89	42.32	42.93	55.24	54.67	61.41	50.67	67.44	71.97	-0.21
21.58	5.90	42.41	43.07	55.07	54.83	61.10	50.73	67.27	71.89	-0.20
21.74	5.89	42.37	43.50	54.99	54.70	61.42	50.80	67.16	72.34	-0.20
21.89	5.91	42.24	43.40	54.99	54.66	61.29	50.80	67.42	72.13	-0.20
22.05	5.90	42.25	43.58	54.97	54.70	61.43	50.83	67.27	72.27	-0.20
22.21	5.89	42.53	43.55	55.10	54.72	61.50	50.85	67.56	72.35	-0.20
22.37	5.93	42.59	44.03	54.69	54.71	61.52	50.88	67.45	72.08	-0.20
22.53	5.91	42.92	44.40	54.81	54.77	61.45	50.90	67.51	72.23	-0.20
22.68	5.92	43.09	44.65	54.91	54.67	61.51	50.90	66.98	72.20	-0.20
22.84	5.91	43.43	45.19	54.68	54.50	61.68	50.80	67.14	72.36	-0.20
23.00	5.92	43.40	45.23	54.83	54.26	61.73	50.82	66.93	72.22	-0.20