

Fixed Attenuator

RCAT-05+

Typical Performance Data

FREQUENCY (GHz)	ATTENUATION (dB)	RETURN LOSS (dB)
0.05	5.01	37.22
0.5	5.02	39.95
1.0	5.03	35.05
1.5	5.05	31.49
2.0	5.06	28.90
2.5	5.07	26.93
3.0	5.09	25.40
3.5	5.11	24.23
4.0	5.14	23.20
4.5	5.16	22.34
5.0	5.18	21.66
5.5	5.21	21.09
6.0	5.24	20.64
6.5	5.26	20.27
7.0	5.29	19.94
7.5	5.31	19.65
8.0	5.35	19.49
8.5	5.39	19.45
9.0	5.41	19.53
9.5	5.43	19.58
10.0	5.47	19.67
10.5	5.49	19.74
11.0	5.52	19.82
11.5	5.54	19.95
12.0	5.58	20.11
12.5	5.60	20.35
13.0	5.63	20.52
13.5	5.65	20.46
14.0	5.70	20.36
14.5	5.73	20.18
15.0	5.78	19.77
15.5	5.81	19.36
16.0	5.89	18.84
16.5	5.95	18.47
17.0	5.98	18.11
17.5	6.00	17.59
18.0	6.00	17.03
18.5	6.05	16.47
19.0	6.11	16.05
19.5	6.17	15.81
20.0	6.24	15.59

