

Fixed Attenuator

RCAT-07+

Typical Performance Data

FREQUENCY (GHz)	ATTENUATION (dB)	RETURN LOSS (dB)
0.05	7.02	32.46
0.5	7.02	34.56
1.0	7.04	32.53
1.5	7.06	30.06
2.0	7.07	27.91
2.5	7.09	26.14
3.0	7.11	24.73
3.5	7.13	23.62
4.0	7.16	22.66
4.5	7.19	21.84
5.0	7.23	21.19
5.5	7.26	20.64
6.0	7.29	20.20
6.5	7.32	19.85
7.0	7.36	19.52
7.5	7.40	19.23
8.0	7.44	19.08
8.5	7.49	18.98
9.0	7.52	19.00
9.5	7.55	18.97
10.0	7.60	18.97
10.5	7.63	18.89
11.0	7.67	18.82
11.5	7.71	18.78
12.0	7.76	18.74
12.5	7.80	18.76
13.0	7.84	18.70
13.5	7.88	18.50
14.0	7.94	18.28
14.5	7.98	18.08
15.0	8.05	17.71
15.5	8.10	17.40
16.0	8.20	17.05
16.5	8.28	16.84
17.0	8.32	16.67
17.5	8.35	16.38
18.0	8.35	16.05
18.5	8.42	15.70
19.0	8.49	15.47
19.5	8.55	15.40
20.0	8.64	15.33

