

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.4mm-FEMALE RETURN LOSS (dB)	2.4mm-MALE RETURN LOSS (dB)
100	0.14	47.3	55.3
1000	0.44	37.5	40.9
3000	0.75	44.2	41.0
4000	0.87	33.4	34.6
5000	0.97	33.8	33.9
6000	1.06	40.3	43.1
7000	1.14	33.1	32.7
8000	1.22	32.4	31.2
9000	1.29	29.4	29.3
10000	1.36	29.3	29.2
11000	1.42	41.6	34.9
12000	1.48	31.3	30.6
13000	1.54	30.7	29.8
14000	1.60	36.4	32.2
15000	1.66	36.1	32.8
16000	1.71	36.2	33.8
17000	1.76	40.9	39.1
18000	1.82	37.8	39.0
19000	1.88	30.1	29.8
20000	1.93	29.8	29.7
21000	1.99	34.7	37.9
22000	2.04	27.8	29.7
23000	2.11	22.6	23.3
24000	2.17	22.0	22.2
25000	2.21	23.5	24.2
26000	2.24	28.2	36.8
27000	2.30	25.4	27.0
28000	2.37	22.2	21.8
29000	2.41	22.9	21.3
30000	2.44	24.7	24.6
32000	2.52	28.3	39.2
34000	2.60	27.3	32.5
36000	2.70	27.0	30.0
38000	2.79	27.6	27.9
40000	2.87	33.3	37.4
42000	2.97	24.7	24.7
44000	3.04	27.9	29.8
46000	3.13	31.1	28.6
48000	3.20	37.9	34.0
50000	3.34	28.7	30.9