

**High Power  
Termination 50Ω, N-Type**

**TERM-500W-14N+**

*Typical Performance Data*

FREQUENCY (MHz)	RETURN LOSS (dB)
500.0	13.63
600.0	15.16
700.0	16.40
800.0	17.57
900.0	18.88
1000.0	19.78
1200.0	20.52
1400.0	24.95
1600.0	26.44
1800.0	27.45
2000.0	24.95
2200.0	38.50
2400.0	43.36
2600.0	26.42
2800.0	25.49
3000.0	33.07
3200.0	31.03
3400.0	29.10
3600.0	25.32
3800.0	30.80
4000.0	24.34
4200.0	27.23
4400.0	22.79
4600.0	24.20
4800.0	22.65
5000.0	23.77
5200.0	26.99
5400.0	20.79
5600.0	26.14
5800.0	22.06
6000.0	24.22
6200.0	29.71
6400.0	23.29
6600.0	23.86
6800.0	24.07
7000.0	27.02
7200.0	26.75
7400.0	22.72
7600.0	27.52
7800.0	30.57
8000.0	34.93
8600.0	30.35
9000.0	30.30
9600.0	35.06
10000.0	24.46
14000.0	24.96
18000.0	16.81

