

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
0.1	0.06	36.97	37.12
0.2	0.08	42.63	42.07
0.3	0.10	45.32	44.40
0.4	0.12	35.28	35.30
0.5	0.13	37.58	36.81
0.6	0.15	43.91	42.50
0.7	0.16	32.84	33.18
0.8	0.16	30.56	30.77
0.9	0.17	39.67	39.84
1.0	0.19	38.47	38.25
1.5	0.24	25.57	25.51
2.0	0.26	29.25	29.04
2.5	0.30	29.04	29.25
3.0	0.34	25.73	25.66
3.5	0.35	29.59	29.46
4.0	0.38	30.37	30.17
4.5	0.41	28.24	27.97
5.0	0.41	33.16	32.45
5.5	0.43	33.46	32.22
6.0	0.45	31.28	30.44
6.5	0.46	35.58	33.66
7.0	0.49	37.77	35.12
7.5	0.51	36.75	35.50
8.0	0.54	35.35	34.37
8.5	0.55	37.11	35.27
9.0	0.57	32.95	32.28
9.5	0.58	31.89	30.84
10.0	0.62	31.98	31.09
10.5	0.64	29.20	28.81
11.0	0.65	29.33	28.61
11.5	0.66	28.74	29.60
12.0	0.68	30.31	34.08
12.5	0.68	28.76	30.21
13.0	0.74	27.49	28.58
13.5	0.73	26.90	27.06
14.0	0.79	28.52	28.29
14.5	0.75	25.97	25.65
15.0	0.80	27.46	27.32
15.5	0.81	26.78	26.98
16.0	0.81	26.99	27.12
16.5	0.84	30.17	29.84
17.0	0.85	28.40	27.61
17.5	0.86	30.20	28.28
18.0	0.87	27.87	27.09