

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
0.01	0.05	38.94	38.17
0.1	0.17	51.00	52.65
0.2	0.25	51.28	48.42
0.4	0.35	41.76	43.76
0.6	0.44	35.55	37.94
0.8	0.51	30.37	30.93
1.0	0.58	27.07	26.71
1.5	0.71	27.83	26.08
2.0	0.83	28.46	27.23
2.5	0.95	23.05	22.14
3.0	1.02	32.72	28.24
3.5	1.12	25.21	24.31
4.0	1.19	32.32	29.16
4.5	1.27	31.45	30.35
5.0	1.34	37.57	52.76
5.5	1.42	30.63	28.63
6.0	1.48	32.75	36.30
6.5	1.55	28.37	29.22
7.0	1.61	25.99	26.63
7.5	1.66	31.20	39.81
8.0	1.73	22.71	22.87
8.5	1.78	23.40	25.39
9.0	1.84	23.06	32.21
9.5	1.91	23.61	24.65
10.0	1.98	25.03	31.19
10.5	2.06	23.56	27.07
11.0	2.15	20.26	21.37
11.5	2.18	27.36	30.17
12.0	2.26	22.27	24.28
12.5	2.30	23.60	24.74
13.0	2.33	28.54	31.91
13.5	2.40	23.15	22.78
14.0	2.44	27.76	31.46
14.5	2.53	22.34	23.24
15.0	2.60	20.89	23.25
15.5	2.65	21.47	25.11
16.0	2.73	19.53	21.75
16.5	2.74	20.38	25.63
17.0	2.83	19.58	21.41
17.5	2.90	18.87	20.14
18.0	3.01	19.80	34.94

