

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
10	0.10	33.75	33.70
100	0.33	48.54	48.50
500	0.77	41.81	40.18
1000	1.11	31.39	31.77
1500	1.37	47.84	45.66
2000	1.61	27.43	27.64
2500	1.81	37.78	44.77
3000	2.00	26.35	26.61
3500	2.17	35.65	39.60
4000	2.34	29.53	30.32
4500	2.49	35.20	36.23
5000	2.64	33.68	37.78
5500	2.78	35.40	41.08
6000	2.92	37.40	35.19
6500	3.05	38.41	35.32
7000	3.19	33.80	31.46
7500	3.31	33.41	30.18
8000	3.44	30.87	28.54
8500	3.57	29.70	27.68
9000	3.68	30.16	27.79
9500	3.82	27.08	25.62
10000	3.92	31.87	28.35
10500	4.03	25.90	24.02
11000	4.14	34.14	27.55
11500	4.25	23.89	22.76
12000	4.36	31.79	27.63
12500	4.48	24.12	22.72
13000	4.57	33.83	26.65
13500	4.68	26.05	24.69
14000	4.77	34.38	28.03
14500	4.87	29.19	27.65
15000	4.97	30.26	29.33
15500	5.06	33.17	32.64
16000	5.16	31.64	32.32
16500	5.25	36.53	39.52
17000	5.35	34.25	35.28
17500	5.44	41.40	35.76
18000	5.54	34.71	33.42