

## Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	N-MALE RETURN LOSS (dB)	SMA-MALE RETURN LOSS (dB)
0.01	0.09	34.36	34.11
0.1	0.30	39.09	37.45
0.2	0.42	33.56	33.27
0.4	0.61	38.70	39.86
0.6	0.76	32.47	32.33
0.8	0.88	34.76	34.78
1.0	0.99	29.46	29.61
1.5	1.23	28.00	28.22
2.0	1.43	31.22	35.22
2.5	1.63	23.58	23.71
3.0	1.78	30.98	31.79
3.5	1.93	28.35	28.67
4.0	2.08	26.27	25.65
4.5	2.22	27.28	35.07
5.0	2.35	33.89	30.41
5.5	2.48	35.67	30.31
6.0	2.60	35.76	30.30
6.5	2.73	28.88	26.30
7.0	2.84	44.55	28.97
7.5	2.96	26.98	26.45
8.0	3.07	32.81	28.41
8.5	3.18	29.50	30.33
9.0	3.29	25.78	25.82
9.5	3.39	32.42	30.22
10.0	3.49	25.72	27.17
10.5	3.60	25.05	24.88
11.0	3.69	32.99	29.62
11.5	3.81	23.39	22.86
12.0	3.90	24.29	23.78
12.5	3.99	31.08	26.56
13.0	4.10	24.50	22.25
13.5	4.17	27.55	26.93
14.0	4.26	30.83	25.76
14.5	4.36	28.70	24.33
15.0	4.44	35.51	28.54
15.5	4.53	31.63	23.78
16.0	4.62	29.76	27.16
16.5	4.70	32.74	31.43
17.0	4.79	29.87	27.63
17.5	4.88	26.35	37.67
18.0	4.96	27.76	31.84