

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
0.01	0.11	35.45	31.54
0.05	0.22	43.56	43.35
0.1	0.31	42.64	42.03
0.5	0.72	47.42	44.38
1.0	1.03	40.23	40.84
1.5	1.28	28.89	29.29
2.0	1.49	28.17	28.74
2.5	1.67	37.69	37.78
3.0	1.85	26.41	26.20
3.5	2.01	27.64	27.45
4.0	2.15	33.82	34.22
4.5	2.31	26.67	26.38
5.0	2.44	32.26	30.53
5.5	2.57	32.61	33.40
6.0	2.70	28.60	28.46
6.5	2.82	33.22	33.99
7.0	2.95	29.12	36.28
7.5	3.06	28.39	29.79
8.0	3.18	28.41	37.33
8.5	3.29	27.49	32.45
9.0	3.41	23.91	26.10
9.5	3.51	27.33	29.29
10.0	3.62	27.78	39.10
10.5	3.73	24.66	25.70
11.0	3.84	22.69	23.83
11.5	3.92	27.68	31.10
12.0	4.02	24.24	25.59
12.5	4.12	22.72	23.15
13.0	4.21	24.43	25.06
13.5	4.30	29.29	27.11
14.0	4.40	24.11	23.50
14.5	4.48	26.29	27.70
15.0	4.58	31.87	26.55
15.5	4.67	33.51	26.85
16.0	4.75	29.62	30.46
16.5	4.84	32.44	30.53
17.0	4.94	42.19	26.54
17.5	5.03	29.76	27.02
18.0	5.10	30.45	33.62

