

Switch SPST , 50Ω

ZFSWHA-1-20+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS C1=-8V,C2=0V (dB) IN-OUT , "ON"	ISOLATION C1=0V,C2=-8V (dB) IN-OUT , "OFF"	VSWR		
			IN	OUT , "ON" (:1)	OUT , "OFF"
0	0.62	90.61	1.15	1.15	1.03
5	0.63	85.48	1.16	1.15	1.03
10	0.69	83.23	1.16	1.15	1.03
100	0.79	67.92	1.15	1.15	1.03
280	0.85	66.96	1.15	1.14	1.03
390	0.92	67.09	1.15	1.14	1.03
445	0.90	67.05	1.16	1.15	1.03
610	0.96	65.89	1.16	1.15	1.04
780	0.99	64.48	1.17	1.16	1.05
890	1.02	63.58	1.18	1.16	1.06
945	1.04	63.07	1.18	1.16	1.07
1000	0.99	62.55	1.18	1.15	1.08
1165	1.09	61.49	1.18	1.15	1.09
1335	1.11	61.45	1.17	1.14	1.12
1445	1.14	61.66	1.16	1.13	1.13
1500	1.09	62.32	1.16	1.12	1.14
1665	1.17	60.72	1.15	1.10	1.17
1835	1.13	60.34	1.14	1.07	1.20
1945	1.22	60.54	1.13	1.06	1.22
2000	1.17	61.08	1.13	1.05	1.23

