

Bias-Tee, Coaxial ZBT-V543-FT+

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	VSWR (:1)	
		RF	RF&DC
0.01	0.79	1.50	1.51
0.1	0.13	1.10	1.09
0.5	0.16	1.02	1.03
0.8	0.18	1.02	1.04
1.0	0.23	1.04	1.06
2.0	0.36	1.07	1.07
3.0	0.51	1.18	1.13
4.0	0.66	1.29	1.24
5.0	0.70	1.36	1.30
6.0	0.74	1.40	1.34
7.0	0.76	1.37	1.34
8.0	0.72	1.29	1.25
9.0	0.68	1.25	1.17
10.0	0.67	1.23	1.15
11.0	0.68	1.15	1.05
12.0	0.72	1.08	1.10
13.0	0.77	1.11	1.21
14.0	0.85	1.16	1.30
15.0	0.92	1.22	1.40
16.0	0.95	1.26	1.46
17.0	0.97	1.29	1.51
18.0	0.98	1.33	1.57
19.0	0.96	1.34	1.54
20.0	0.91	1.33	1.49
21.0	0.91	1.29	1.46
22.0	0.91	1.16	1.30
23.0	0.91	1.05	1.11
24.0	0.92	1.10	1.05
25.0	0.94	1.16	1.09
26.0	0.99	1.20	1.16
27.0	1.02	1.25	1.26
28.0	1.03	1.25	1.31
29.0	1.02	1.26	1.35
30.0	1.05	1.29	1.36
31.0	1.04	1.29	1.34
32.0	1.15	1.28	1.33
33.0	1.26	1.25	1.32
34.0	1.18	1.22	1.28
35.0	1.26	1.23	1.33
36.0	1.27	1.30	1.42
37.0	1.21	1.30	1.36
38.0	1.17	1.32	1.22
39.0	1.25	1.38	1.14
40.0	1.23	1.56	1.27
41.0	1.45	1.73	1.45
42.0	1.50	1.83	1.52
43.0	1.59	1.80	1.40
44.0	1.57	1.59	1.21
45.0	1.60	1.38	1.12
46.0	1.60	1.20	1.17
47.0	1.68	1.27	1.37
48.0	1.66	1.28	1.47
49.0	1.74	1.26	1.50
50.0	1.67	1.25	1.46
51.0	1.66	1.29	1.44
52.0	1.73	1.25	1.36
53.0	1.73	1.15	1.17
54.0	1.86	1.11	1.13

