

Hand-Flex Coaxial Cable

086-11SMRSM+

SMA-Male to Right Angle SMA-Male

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE RETURN LOSS (dB)
100	0.06	39.1	40.3
150	0.08	41.3	41.6
200	0.10	40.3	41.3
250	0.11	42.4	43.7
300	0.12	50.5	49.1
350	0.13	54.7	53.4
400	0.14	46.8	50.6
450	0.15	43.2	46.9
500	0.16	41.0	45.6
550	0.17	41.0	45.3
600	0.18	43.4	46.4
650	0.18	47.0	45.0
700	0.19	52.2	44.9
750	0.20	48.8	44.0
800	0.20	44.0	43.8
850	0.21	41.6	44.1
950	0.22	44.9	47.8
1000	0.23	49.3	47.3
1500	0.28	41.5	54.6
2000	0.31	38.4	40.2
2500	0.35	47.8	50.2
3000	0.39	45.5	40.3
3500	0.42	43.1	43.5
4000	0.46	34.0	30.7
4500	0.49	31.3	29.1
5000	0.51	34.7	33.0
5500	0.54	29.5	26.7
6000	0.57	29.9	28.2
6500	0.59	32.8	31.6
7000	0.62	33.5	31.6
7500	0.64	39.1	38.6
8000	0.66	40.6	38.6
8500	0.68	46.0	45.0
9000	0.71	33.7	33.6
9500	0.73	38.3	37.2
10000	0.75	38.3	36.3
10500	0.77	29.3	29.3
11000	0.80	31.6	31.5
11500	0.81	32.8	30.8
12000	0.84	23.0	22.6
12500	0.84	28.9	27.8
13000	0.88	30.5	28.0
13500	0.88	23.5	23.1
14000	0.89	37.2	29.8
14500	0.93	26.8	26.4
15000	0.95	26.8	25.5
15500	0.96	30.7	29.7
16000	0.98	28.9	26.3
16500	1.04	23.6	22.4
17000	1.02	28.6	23.5
17500	1.06	22.3	19.8
18000	1.07	27.0	22.6



ISO 9001 ISO 14001 AS 9100 CERTIFIED



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
086-11SMRSM+
6/21/2018
Page 1 of 1