

Panel Mounted Structures



Connector Adapters / Cable Organizers
Power Splitters / Combiners
Directional Couplers
Fixed Attenuators

Mini-Circuits' panel-mounted structures provide clean, organized management of cable runs and connections in complex, high-volume test setups. Multiple connector adapters, power splitters, directional couplers and other essential RF components and test accessories can be integrated efficiently within the test system. Custom configurations are available upon request.



PO Box 350166, Brooklyn, NY 11235-0003
+1 718-934-4500 | testsolutions@minicircuits.com
www.minicircuits.com


Connector Adapter / Cable Organizer Panels

ZT-96KFLL-KF50+ | DC to 40 GHz

96 x connector adapters:

2.92 mm female to 2.92 mm female

19" width, 5U height




ZT-182 | DC to 11 GHz

48 x connector adapters:

N-type female to N-type female

19" width, 4U height



ZT-183 | DC to 18 GHz

48 x connector adapters:

N-type female to SMA female

19" width, 4U height



ZT-240 | DC to 6 GHz

24 x connector adapters:

N-type female to N-type female

19" width, 4U height

Extended mounting brackets



ZT-240BK | DC to 6 GHz

24 x connector adapters:

N-type female to N-type female

19" width, 4U height

Black anodized panel



Splitter / Combiner Panels

ZT-245 | 300 to 1000 MHz

Splitter / Combiner Panel:

1 x 8-Way Splitter / Combiner

19" width, 1U height

SMA female connectors



ZT-277 | 600 to 6000 MHz

Splitter / Combiner Panel:

3 x 4-Way Splitter / Combiners

19" width, 1U height

SMA female connectors



ZT-257 | 600 to 6000 MHz

Splitter / Combiner Panel:

4 x 4-Way Splitter / Combiners

19" width, 1U height

SMA female connectors



ZT-184 | 500 to 6000 MHz

Splitter / Combiner Panel:

10 x 4-Way Splitter / Combiners

19" width, 3U height

SMA female connectors




ZT-304 | 500 to 6000 MHz

Splitter / Combiner Panel:

8 x 2-Way Splitter / Combiners

19" width, 1U height

SMA female connectors



ZT-304BK | 500 to 6000 MHz

Splitter / Combiner Panel:

8 x 2-Way Splitter / Combiners

19" width, 1U height (black anodized panel)

SMA female connectors




ZT-255 | 500 to 8500 MHz

Splitter / Combiner Panel:

8 x 2-Way Splitter / Combiners

19" width, 2U height

SMA female connectors



ZT-256 | DC to 18 GHz

Splitter / Combiner Panel:

12 x 2-Way Resistive Splitter / Combiners

19" width, 2U height

SMA female connectors




ZT-229B | 0.5 to 600 MHz

Splitter / Combiner Panel:

16 x 2-Way Splitter / Combiners

19" width, 2U height

SMA female connectors



ZT-222 | 350 to 6000 MHz

Splitter / Combiner Panel:

20 x 2-Way Splitter / Combiners

19" width, 4U height

N-type female connectors



Directional Coupler Panels

ZT-230 | 1 to 500 MHz

Directional Coupler Panel:

8 x 10 dB Directional Couplers

19" width, 2U height

SMA female connectors



Fixed Attenuator Panels

ZT-275 | DC to 18 GHz

Attenuator Panel:

10 x 30 dB Fixed Attenuators

19" width, 2U height

SMA female connectors

