

Test Cable

50Ω 3FT DC to 18 GHz


CBL-3FT-SFSM+



Maximum Ratings

Operating Temperature	-55°C to 105°C
Storage Temperature	-55°C to 105°C
Permanent damage may occur if any of these limits are exceeded.	


Shielding Effectiveness	>100 dB
Power Handling at 25°C	891W Max. at 0.4 GHz
	539W Max. at 1 GHz
	363W Max. at 2 GHz
	180W Max. at 6 GHz
	117W Max. at 12 GHz
Jacket	88W Max. at 18 GHz
	Blue FEP



Outline Dimensions (inch)

A		B	C	D	E	T		wt
Feet	Meters	.51	.00	.42	.312	Feet	Meters	grams
3.00	0.91	12.95	0.00	10.67	7.92	0.09	0.03	90

Cable Cross Section



Cable Construction	
Inner Conductor	Solid Silver Plated Copper Clad Steel
Dielectric	Solid PTFE
Shield	Silver-Plated Copper Flat Ribbon Braid Aluminum-Polyimide Tape Interlayer 36 GA Silver-Plated Copper Braid (90%k)
Jacket	Blue FEP
Connectors	
- passivated stainless steel - captive contact - thick wall interface (SMA) - gold plated beryllium copper center contacts - PTFE dielectric	

Product Guarantee*

Mini-Circuits® will repair or replace your test cable at its option if the connector attachment fails within six months of shipment. This guarantee excludes cable or connector interface damage from misuse or abuse.

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- RoHS compliant
- wideband coverage, DC to 18 GHz
- extra rugged construction with strain relief for longer life
- stainless steel SMA connectors for long mating-cycle life
- useful over temperature range, -55°C to 105°C
- triple shield cable for excellent shielding effectiveness
- flexible for easy connection & bend radius
- superior stability of insertion loss, VSWR & phase vs. flexing
- 6 month guarantee*

Applications

- high volume production test stations
- research & development labs
- environmental & temperature test chambers
- replacement for OEM test port cables
- field RF testing
- cellular infrastructure site testing

CASE STYLE: GM1133-3

Connectors	Model
Conn1 SMA-FEMALE	Conn2 SMA-MALE CBL-3FT-SFSM+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Electrical Specifications at 25°C

FREQ. (GHz)	LENGTH (FT)	INSERTION LOSS (dB)				RETURN LOSS (dB)			
		DC-2.5 GHz	2.5-6 GHz	6-12 GHz	12-18 GHz	DC-2.5 GHz	2.5-6 GHz	6-12 GHz	12-18 GHz
$f_L - f_U$		Typ. Max.	Typ. Max.	Typ. Max.	Typ. Max.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.
DC-18	3	0.6 0.8	1.0 1.3	1.5 1.9	1.9 2.45	30 23	30 20	27 17	27 17

Custom sizes available, consult factory.

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	
		SMA-FEMALE	SMA-MALE
10.00	0.04	44.97	45.82
1000.00	0.38	34.80	35.88
2000.00	0.55	32.82	33.72
2500.00	0.62	35.30	36.37
4000.00	0.81	41.00	40.63
5000.00	0.92	33.79	36.43
6000.00	1.03	30.21	32.41
7000.00	1.12	28.55	30.38
8000.00	1.21	28.92	28.62
9000.00	1.33	28.10	25.55
10000.00	1.38	26.76	24.20
12000.00	1.55	28.14	23.84
14000.00	1.71	28.13	23.75
15000.00	1.76	27.20	24.10
18000.00	1.91	22.69	24.57



Test Cable, SMA-Female/SMA-Male

CBL-3FT-SFSM+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-FEMALE RETURN LOSS (dB)	SMA-MALE RETURN LOSS (dB)
10	0.04	44.97	45.82
100	0.11	43.19	43.88
250	0.18	41.17	41.59
500	0.26	38.31	38.51
750	0.33	36.95	37.93
1000	0.38	34.80	35.88
1250	0.43	34.41	35.50
1500	0.47	33.80	35.28
1750	0.51	32.03	32.75
2000	0.55	32.82	33.72
2250	0.58	33.32	34.55
2500	0.62	35.30	36.37
2750	0.65	39.85	39.49
3000	0.68	40.51	40.16
3500	0.75	41.82	41.32
4000	0.81	41.00	40.63
4500	0.86	37.54	39.03
5000	0.92	33.79	36.43
5500	0.97	31.25	33.59
6000	1.03	30.21	32.41
6500	1.05	29.21	30.83
7000	1.12	28.55	30.38
7500	1.18	27.52	28.57
8000	1.21	28.92	28.62
8500	1.25	29.13	27.48
9000	1.33	28.10	25.55
9500	1.33	28.22	24.97
10000	1.38	26.76	24.20
11000	1.47	25.94	23.85
12000	1.55	28.14	23.84
13000	1.62	28.57	23.60
14000	1.71	28.13	23.75
15000	1.76	27.20	24.10
16000	1.80	23.45	23.65
17000	1.86	23.07	23.99
18000	1.91	22.69	24.57

REV. X1
CBL-3FT-SFSM+
061114
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Typical Performance Curves



Outline Dimensions



* OVERALL CONNECTOR OR CABLE & BOOT DIMENSION
(CONNECTOR SHAPE MAY VARY)

GM1133 SERIES
SMA FEMALE (CONN-1)
SMA MALE (CONN-2)

CASE STYLE #	A		B	C	D	E	T		WEIGHT GRAMS
	FEET	METERS					FEET	METERS	
GM1133-1	1.00	.30	.51 (12.95)	-	.42 (10.67)	.312 (7.92)	.06	.02	51
GM1133-1.5	1.50	.46					.06	.02	60
GM1133-1.64	1.64	.50					.06	.02	63
GM1133-2	2.00	.61					.06	.02	70
GM1133-3	3.00	.91					.09	.03	90
GM1133-3.28	3.28	1.00					.10	.03	95
GM1133-4	4.00	1.22					.12	.04	109
GM1133-5	5.00	1.52					.15	.05	129
GM1133-6	6.00	1.83					.18	.05	148
GM1133-6.56	6.56	2.00					.20	.06	159
GM1133-10	10.00	3.05					.30	.09	226
GM1133-16.4	16.40	5.00					.49	.15	351
GM1133-25	25.00	7.62					.75	.23	519
GM1133-32.8	32.80	10.00					.98	.30	671
GM1133-65.6	65.60	20.00					1.97	.60	1310

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Note:

1. Flexible Coaxial Cable.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 105°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except -105°C
Mechanical Flexing	20,000 cycles During each cycle, cable flexed from 90° through 0° to -90° and back with a Radii of 3 inches	- - -