


**THE BIG DEAL**

- 5.3 dB Slope from DC to 28 GHz, can work up to 30 GHz
- Small Package 2 x 2 mm MCLP
- Excellent Return Loss, 20 dB typ.
- Patent pending

*Generic photo used for illustration purposes only*

CASE STYLE: MC1630-1

**APPLICATIONS**

- Cellular Infrastructure
- 5G
- Wideband Communications
- Test Instrumentation
- Defense

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

**PRODUCT OVERVIEW**

EQY-5-283+ is an absorptive Gain Equalizer fabricated using highly repetitive GaAs IPD MMIC process incorporating resistors, capacitors and inductors having negative insertion loss slope. EQY-5-283+ has a nominal attenuation slope of 5.3 dB and is packaged in tiny 2 x 2 mm, 6-Lead MCLP™ package.

**KEY FEATURES**

| Feature                                           | Advantages                                                                                                                                                                                                 |
|---------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Negative Insertion Loss Slope vs. Frequency       | Useful for compensating negative gain slope of amplifiers, receivers, transmitters to achieve flat gain versus frequency.                                                                                  |
| Wide range of values 3,4,5,6 dB                   | Enables circuit designer to change nominal insertion loss values without board redesign making the EQY series ideal for select at test application.                                                        |
| Wideband operation, DC to 28 GHz                  | Supports a wide array of applications including wireless cellular, microwave communications, satellite, defense and aerospace, medical broadband and optic applications.                                   |
| Excellent Power Handling Capability up to +30 dBm | Enables its use at the output of a variety of amplifiers                                                                                                                                                   |
| Small Size and simple to use (2 mm x 2 mm)        | As a single chip solution, the EQY series occupies less board space than a lumped or distributed element approach, minimizes component count and ensures repeatable performance over wide frequency range. |

\*GaAs IPD (Gallium Arsenide Integrated Passive Device)

REV. A  
ECO-014607  
EQY-5-283+  
GY/RS/CP  
MCL NY  
220817

**ELECTRICAL SPECIFICATIONS<sup>1</sup> AT 25°C, 50Ω, UNLESS OTHERWISE NOTED.**

| Parameter       | Condition (GHz) | Min. | Typ. | Max. | Units |
|-----------------|-----------------|------|------|------|-------|
| Frequency Range |                 | DC   |      | 28   | GHz   |
| Insertion Loss  | 0.01            | 5.6  | 5.9  | 6.2  | dB    |
|                 | 10              | 3.8  | 4.4  | 4.9  |       |
|                 | 20              | 1.3  | 1.8  | 2.2  |       |
|                 | 28              | 0.3  | 0.6  | 1.2  |       |
|                 | 30              | —    | 0.6  | —    |       |
| VSWR            | 0.01 - 10       | —    | 1.16 | —    | :1    |
|                 | 10 - 20         | —    | 1.12 | —    |       |
|                 | 20 - 28         | —    | 1.12 | —    |       |
|                 | 28 - 30         | —    | 1.12 | —    |       |

1. Measured on Mini-Circuits Characterization Test Board TB-EQY-5-283+. See Characterization Test Circuit (Fig. 1)

**MAXIMUM RATINGS<sup>2</sup>**

| Parameter                   | Ratings        |
|-----------------------------|----------------|
| Operating Case Temperature  | -55°C to 105°C |
| Storage Temperature         | -65°C to 150°C |
| RF Input Power <sup>3</sup> | +30 dBm        |

2. Permanent damage may occur if any of these limits are exceeded.

3. Derates linearly to 26 dBm at 105°C



Mini-Circuits



MICROWAVE

# Gain Equalizer

EQY-5-283+

50Ω 5dB DC to 28 GHz

## SIMPLIFIED SCHEMATIC & PAD DESCRIPTION



| Function | Pad Number       | Description   |
|----------|------------------|---------------|
| RF-IN    | 2                | RF-Input pad  |
| RF-OUT   | 5                | RF-Output pad |
| GND      | 1,3,4,6 & Paddle | Ground        |

## CHARACTERIZATION TEST CIRCUIT





Fig 1. Block Diagram of Test Circuit used for characterization. Test Board TB-EQY-5-283+  
Conditions: Attenuation & Return Loss Pin=0 dBm

## PRODUCT MARKING



Marking may contain other features or characters for internal lot control



MICROWAVE

# Gain Equalizer

**EQY-5-283+**

Mini-Circuits

50Ω 5dB DC to 28 GHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

|                                                      |                                                              |
|------------------------------------------------------|--------------------------------------------------------------|
| Performance Data                                     | Data Table                                                   |
|                                                      | Swept Graphs                                                 |
| Case Style                                           | MC1630-1 Plastic package, Lead finish: Matte-tin             |
| Tape & Reel<br>Standard quantities available on reel | F66<br>7" reels with 20, 50, 100, 200, 500, 1K or 2K devices |
| Suggested Layout for PCB Design                      | PL-663                                                       |
| Evaluation Board                                     | TB-EQY-5-283+ & TB-EQY-5-283C+                               |
| Environmental Ratings                                | ENV08T1                                                      |


## ESD RATING

Human Body Model (HBM): Class 2 (Pass 2000V) in accordance with ANSI/ESD STM 5.1 - 2001 Machine.

## MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D.

## MSL TEST FLOW CHART




## Typical Performance Data


| FREQ. | INSERTION LOSS |       |         | INPUT VSWR |       |         | OUTPUT VSWR |       |         |
|-------|----------------|-------|---------|------------|-------|---------|-------------|-------|---------|
| (MHz) | (dB)           |       |         | (:1)       |       |         | (:1)        |       |         |
|       | @-55°C         | @25°C | @+105°C | @-55°C     | @25°C | @+105°C | @-55°C      | @25°C | @+105°C |
| 10    | 5.82           | 5.93  | 5.94    | 1.18       | 1.19  | 1.19    | 1.18        | 1.19  | 1.20    |
| 100   | 5.82           | 5.94  | 5.95    | 1.12       | 1.13  | 1.14    | 1.11        | 1.13  | 1.14    |
| 500   | 5.83           | 5.95  | 5.96    | 1.12       | 1.13  | 1.13    | 1.11        | 1.13  | 1.13    |
| 1000  | 5.83           | 5.95  | 5.95    | 1.13       | 1.13  | 1.14    | 1.12        | 1.13  | 1.13    |
| 2000  | 5.77           | 5.89  | 5.91    | 1.16       | 1.17  | 1.17    | 1.16        | 1.16  | 1.17    |
| 3000  | 5.68           | 5.81  | 5.82    | 1.19       | 1.20  | 1.21    | 1.19        | 1.19  | 1.20    |
| 4000  | 5.57           | 5.70  | 5.71    | 1.22       | 1.22  | 1.23    | 1.23        | 1.22  | 1.23    |
| 5000  | 5.44           | 5.57  | 5.57    | 1.22       | 1.21  | 1.21    | 1.25        | 1.23  | 1.23    |
| 6000  | 5.29           | 5.42  | 5.41    | 1.22       | 1.21  | 1.20    | 1.25        | 1.23  | 1.23    |
| 7000  | 5.10           | 5.23  | 5.23    | 1.23       | 1.22  | 1.21    | 1.27        | 1.25  | 1.24    |
| 8000  | 4.88           | 5.01  | 5.01    | 1.25       | 1.24  | 1.24    | 1.30        | 1.28  | 1.28    |
| 9000  | 4.61           | 4.73  | 4.71    | 1.24       | 1.23  | 1.23    | 1.29        | 1.26  | 1.26    |
| 10000 | 4.30           | 4.42  | 4.39    | 1.15       | 1.14  | 1.13    | 1.19        | 1.16  | 1.15    |
| 11000 | 4.02           | 4.15  | 4.14    | 1.08       | 1.06  | 1.06    | 1.04        | 1.02  | 1.01    |
| 12000 | 3.79           | 3.92  | 3.92    | 1.15       | 1.13  | 1.12    | 1.12        | 1.09  | 1.09    |
| 13000 | 3.54           | 3.67  | 3.65    | 1.18       | 1.15  | 1.13    | 1.15        | 1.11  | 1.10    |
| 14000 | 3.26           | 3.39  | 3.35    | 1.15       | 1.13  | 1.12    | 1.11        | 1.09  | 1.10    |
| 15000 | 3.01           | 3.13  | 3.11    | 1.21       | 1.18  | 1.19    | 1.17        | 1.16  | 1.17    |
| 16000 | 2.79           | 2.92  | 2.92    | 1.30       | 1.30  | 1.29    | 1.28        | 1.29  | 1.28    |
| 17000 | 2.54           | 2.70  | 2.70    | 1.35       | 1.36  | 1.35    | 1.36        | 1.36  | 1.34    |
| 18000 | 2.25           | 2.39  | 2.38    | 1.29       | 1.27  | 1.26    | 1.32        | 1.27  | 1.26    |
| 19000 | 1.92           | 2.06  | 2.04    | 1.18       | 1.14  | 1.15    | 1.18        | 1.11  | 1.10    |
| 20000 | 1.62           | 1.80  | 1.80    | 1.14       | 1.11  | 1.13    | 1.01        | 1.03  | 1.03    |
| 21000 | 1.46           | 1.60  | 1.61    | 1.23       | 1.15  | 1.13    | 1.13        | 1.07  | 1.05    |
| 22000 | 1.31           | 1.43  | 1.44    | 1.19       | 1.16  | 1.11    | 1.12        | 1.10  | 1.05    |
| 23000 | 1.10           | 1.24  | 1.26    | 1.10       | 1.12  | 1.08    | 1.05        | 1.06  | 1.05    |
| 24000 | 0.91           | 1.07  | 1.10    | 1.08       | 1.09  | 1.08    | 1.07        | 1.05  | 1.09    |
| 25000 | 0.77           | 0.92  | 0.97    | 1.14       | 1.10  | 1.11    | 1.12        | 1.09  | 1.12    |
| 26000 | 0.63           | 0.80  | 0.86    | 1.14       | 1.12  | 1.13    | 1.06        | 1.10  | 1.11    |
| 27000 | 0.50           | 0.69  | 0.76    | 1.10       | 1.07  | 1.08    | 1.01        | 1.04  | 1.04    |
| 28000 | 0.46           | 0.62  | 0.69    | 1.07       | 1.05  | 1.04    | 1.01        | 1.04  | 1.04    |
| 29000 | 0.45           | 0.60  | 0.65    | 1.09       | 1.06  | 1.05    | 1.04        | 1.07  | 1.05    |
| 30000 | 0.44           | 0.66  | 0.69    | 1.18       | 1.28  | 1.25    | 1.13        | 1.22  | 1.19    |
| 31000 | 0.57           | 0.78  | 0.88    | 1.52       | 1.54  | 1.56    | 1.46        | 1.48  | 1.51    |
| 32000 | 0.85           | 0.96  | 1.13    | 1.99       | 1.80  | 1.85    | 1.92        | 1.78  | 1.85    |
| 33000 | 0.79           | 1.03  | 1.09    | 1.95       | 1.85  | 1.83    | 1.99        | 1.92  | 1.90    |
| 34000 | 0.54           | 0.83  | 0.76    | 1.55       | 1.58  | 1.51    | 1.59        | 1.62  | 1.51    |
| 35000 | 0.54           | 0.73  | 0.72    | 1.30       | 1.30  | 1.30    | 1.25        | 1.16  | 1.10    |
| 36000 | 0.67           | 0.84  | 0.82    | 1.27       | 1.28  | 1.24    | 1.03        | 1.08  | 1.10    |
| 37000 | 0.69           | 0.84  | 0.89    | 1.27       | 1.19  | 1.15    | 1.19        | 1.14  | 1.09    |
| 38000 | 0.64           | 0.84  | 0.88    | 1.20       | 1.18  | 1.19    | 1.12        | 1.05  | 1.07    |
| 39000 | 0.68           | 0.93  | 0.96    | 1.43       | 1.41  | 1.45    | 1.24        | 1.28  | 1.35    |
| 40000 | 0.87           | 1.19  | 1.12    | 1.77       | 1.79  | 1.76    | 1.59        | 1.71  | 1.68    |

## Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE  
INPUT POWER = -5 dBm




INPUT VSWR vs. TEMPERATURE  
INPUT POWER = -5 dBm




OUTPUT VSWR vs. TEMPERATURE  
INPUT POWER = -5 dBm



### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE #.  | A              | B              | C              | D              | E             | F             | G             | H             | J             | K             | L              | M              | N             | P             |
|----------|----------------|----------------|----------------|----------------|---------------|---------------|---------------|---------------|---------------|---------------|----------------|----------------|---------------|---------------|
| MC1630-1 | .079<br>(2.00) | .079<br>(2.00) | .039<br>(1.00) | .047<br>(1.20) | .024<br>(.60) | .010<br>(.25) | .014<br>(.35) | .026<br>(.65) | .008<br>(.20) | .002<br>(.05) | .106<br>(2.70) | .049<br>(1.25) | .026<br>(.65) | .031<br>(.80) |


| CASE #.  | Q             | R             | WT, GRAM |
|----------|---------------|---------------|----------|
| MC1630-1 | .012<br>(.30) | .012<br>(.30) | .006     |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

#### Notes:

- Case material: Plastic.
- Termination finish:  
For RoHS Case Styles: Tin-Silver over Nickel plated or Matte-Tin plated (See Data sheet).  
All models, (+) suffix.
- Lead #1 identifier shall be located in the cross-hatched area shown.  
Identifier may be either a molded or marked feature.

# Tape & Reel Packaging TR-F66



| Tape Width,<br>mm | Device Cavity<br>Pitch, mm | Reel Size,<br>inches | Devices per Reel<br>see note  |                  |
|-------------------|----------------------------|----------------------|-------------------------------|------------------|
| 8                 | 4                          | 7                    | Small<br>quantity<br>standard | 20               |
|                   |                            |                      |                               | 50               |
|                   |                            |                      |                               | 100              |
|                   |                            |                      |                               | 200              |
|                   |                            |                      |                               | 500              |
|                   |                            | 7                    | Standard                      | 1000, 2000, 3000 |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)





INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


## THIRD ANGLE PROJECTION



## REVISIONS

| REV | ECN No.    | DESCRIPTION | DATE     | DR | AUTH |
|-----|------------|-------------|----------|----|------|
| OR  | ECO-001053 | NEW RELEASE | 12/18/19 | GF | IL   |
|     |            |             |          |    |      |
|     |            |             |          |    |      |


SUGGESTED MOUNTING CONFIGURATION  
FOR MC1630-1 CASE STYLE,

**NOTES:**

1. TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS  $.0066 \pm .001$ . COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
2. UNIT FOOT PRINT IS OPTIMIZED FOR PERFORMANCE AND IS DIFFERENT FROM CASE STYLE MC1630-1 RECOMMENDATIONS.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS  $\pm$ 3 PL DECIMALS  $\pm$  .005ANGLES  $\pm$ FRACTIONS  $\pm$ 

DRAWN

GF

12/16/19

CHECKED

IL

12/18/19

APPROVED

IL

12/18/19



**Mini-Circuits®**

13 Neptune Avenue  
Brooklyn NY 11235

**PL, MC1630-1, TB-EQY-X-453+  
TB-EQY-X-453C+**

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-663

REV:

OR

FILE: 98PL663

SCALE:

15:1

SHEET:

1 OF 1


ASHEETA1.DWG REV:A DATE:01/12/95

Mini-Circuits®


THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

# Evaluation Board and Circuit


SEE DETAIL "A"



INDEX — DUT



DETAIL "A"  
(SCALE 5:1)



SCHEMATIC DIAGRAM  
(SCALE 5:1)

| Function | Pad     |
|----------|---------|
| RF-IN    | 2       |
| RF-OUT   | 5       |
| GND      | 1,3,4,6 |

## Notes:

- 2.4mm Female Connectors.
- PCB Material: Roger R04350B or equivalent,  
Dielectric constant=3.5, Thickness=0.0066 inch

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                      | Reference/Spec                                                  |
|--------------------------------|--------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------|
| Operating Temperature          | -40° to 85°C or -45° to 85°C<br>Ambient Environment                                                                            | Individual Model Data Sheet                                     |
| Storage Temperature            | -55° to 100° C or -65° to 150°<br>Ambient Environment                                                                          | Individual Model Data Sheet                                     |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                                      | MIL-STD-202, Method 107, Condition A-3, except +100°C           |
| Mechanical Shock               | 1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only                                                                               | MIL-STD-883, Method 2002, Condition B, except Y1 direction only |
| Vibration (Variable Frequency) | 50g peak                                                                                                                       | MIL-STD-883, Method 2007, Condition B                           |
| Autoclave                      | 15 psig, 100% RH, 121°C, 96 hours                                                                                              | JESD22-A102, Condition C                                        |
| HAST                           | 130°C, 85% RH, 96 hours                                                                                                        | JESD22-A110                                                     |
| Solderability                  | 10X Magnification                                                                                                              | J-STD-002, Para 4.2.5, Test S, 95% Coverage                     |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 240°C peak<br>Pb-Free Process: 260°C peak                                                               | J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1                   |
| Moisture Sensitivity: Level 1  | Bake at 125°C for 24 hours<br>Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak                                 | J-STD-020                                                       |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + | MIL-STD-202, Method 215                                         |



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition        | Reference/Spec |
|---------------|----------------------------------|----------------|
|               | monoethanolamine at 63°C to 70°C |                |