

Ceramic

Low Pass Filter

LFCG-490+

50Ω

DC to 490 MHz



Generic photo used for illustration purposes only

CASE STYLE: GE0805C-2

The Big Deal

- Very good rejection, 45 dB typical
- Rugged, ceramic construction
- Tiny size, 0.079" x 0.049" x 0.037" (0805)
- Good power handling, 3.5W

Product Overview

Mini-Circuits' LFCG-490+ is an LTCC low pass filter with a passband from DC to 490 MHz, supporting a variety of applications. This model provides 1.5 dB typical passband insertion loss and provides a very good stopband rejection due to strategically constructed layout with minimal interaction between components. It handles up to 3.5W RF input power and provides a wide operating temperature range from -55 to +125°C. Housed in a tiny 0805 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts and with minimal performance variation due to parasitics.

Key Features

Feature	Advantages
Ultra-wide stopband	The LTCC lowpass filter provides a very good stopband rejection until 8.5 GHz suitable for high end applications.
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.
Tiny size (0.079" x 0.049" x 0.037")	Saves space in dense circuit board layouts and minimizes the effects of parasitics.
Good power handling, 3.5W	Supports a wide range of system power requirements.
Wrap-around terminations	Provides excellent solderability and easy visual inspection

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Low Pass Filter

50Ω

DC to 490 MHz

LFCG-490+



Generic photo used for illustration purposes only
CASE STYLE: GE0805C-2

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Features

- Low loss, 1.5 dB typical
- High rejection 45 dB typical
- Good power handling, 3.5W
- Extremely small size 0805 (2.0mm x 1.25mm)
- Temperature stable
- LTCC construction

Applications

- Harmonic Rejection
- VHF/UHF transmitters / receivers
- Military radar applications
- Test and measurement
- Telecommunications & broadband wireless applications
- Satcom modems

Functional Schematic



Electrical Specifications^{1,2} at 25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC-F1	DC - 490	—	1.5	2	dB
	Freq. Cut-Off	F2	590	—	3.0	—	dB
	Return Loss	DC-F1	DC - 490	—	14	—	dB
Stop Band	Rejection Loss	F3-F4	800 - 960	20	50	—	dB
		F4-F5	960 - 1500	40	48	—	dB
		F5-F6	1500 - 3000	35	45	—	dB
		F6-F7	3000 - 8500	—	15	—	dB

1. DC de-coupling capacitors are required in Applications where DC voltage and/or current is present at either input or output ports. Please contact Mini-Circuits for alternatives if DC pass from IN-OUT is required.
2. Measured on Mini-Circuits Characterization Test Board TB-799+

Maximum Ratings





Operating Temperature	-55°C to 125°C
Storage Temperature	-55°C to 125°C
RF Power Input*	3.5W max. @ 25°C

*Passband rating, derate linearly to 0.9W at 125°C ambient
Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	0.22	33.05
100	0.38	20.89
300	0.75	16.37
400	0.99	24.15
490	1.46	20.86
590	3.26	12.95
685	20.48	3.94
720	31.29	3.16
800	59.71	1.83
960	58.62	0.74
1500	51.64	0.23
3000	46.62	0.14
4200	30.44	0.28
6100	35.45	0.29
6600	29.96	0.58
7000	40.92	2.84
7600	31.96	1.13
8000	27.65	0.77
8400	26.02	0.68
8500	25.93	0.78

Typical Frequency Response



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




Pad Connections

INPUT	8
OUTPUT	4
GROUND	1,2,3,5,6,7


Product Marking: LP

Demo Board MCL P/N: TB-799+
Suggested PCB Layout (PL-429)



- NOTES:
1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- Legend:
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
 - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F	G	Wt.
.079	.049	.037	.014	.012	.012	.026	grams
2.00	1.25	0.95	0.35	0.30	0.30	0.65	.008

Note: Please refer to case style drawing for details

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp






Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
10	0.24	0.29	0.32	34.35	32.94	31.83	35.59	34.03	32.46
40	0.26	0.31	0.35	30.83	28.30	27.13	29.88	27.62	26.57
100	0.30	0.37	0.42	26.03	24.01	22.73	23.18	21.85	20.85
200	0.40	0.50	0.56	20.44	19.68	18.89	16.80	16.46	15.76
300	0.57	0.69	0.76	18.52	18.24	17.78	15.95	15.78	15.25
400	0.78	0.93	1.03	20.94	20.89	20.29	23.55	23.22	22.74
420	0.84	1.00	1.11	22.05	21.86	21.08	28.61	28.54	28.13
460	1.01	1.19	1.31	23.11	22.72	21.76	25.03	26.12	26.44
490	1.21	1.39	1.53	21.45	21.43	20.83	20.03	20.50	20.44
500	1.29	1.47	1.62	20.68	20.76	20.29	19.02	19.37	19.26
590	3.10	3.14	3.25	15.62	18.54	20.42	12.02	13.10	13.78
600	3.81	3.70	3.72	11.94	14.88	17.74	10.08	11.50	12.58
685	22.49	20.40	18.64	1.30	1.82	2.30	3.31	3.98	4.82
700	27.16	24.88	22.92	1.03	1.46	1.81	3.01	3.62	4.37
720	33.82	31.22	28.99	0.76	1.12	1.36	2.62	3.16	3.81
800	57.63	59.66	60.32	0.26	0.54	0.59	1.49	1.80	2.16
850	55.93	56.20	56.50	0.07	0.33	0.34	1.05	1.28	1.54
900	57.10	57.34	57.48	0.04	0.21	0.20	0.78	0.97	1.16
960	58.11	58.35	58.57	0.11	0.12	0.11	0.57	0.71	0.86
1000	58.82	58.89	59.05	0.12	0.10	0.09	0.49	0.62	0.75
1100	62.45	61.68	61.44	0.23	0.05	0.04	0.37	0.47	0.56
1500	50.62	51.53	52.28	0.23	0.08	0.08	0.19	0.26	0.31
2000	44.65	45.05	45.29	0.24	0.07	0.11	0.12	0.18	0.22
2200	44.19	44.50	44.62	0.23	0.08	0.11	0.09	0.15	0.19
2300	44.15	44.38	44.49	0.25	0.11	0.14	0.08	0.15	0.18
2400	44.16	44.37	44.41	0.30	0.15	0.18	0.06	0.13	0.17
2500	44.31	44.45	44.50	0.31	0.17	0.20	0.07	0.14	0.18
2700	44.93	45.04	44.99	0.36	0.19	0.24	0.07	0.15	0.20
2900	45.90	45.91	45.74	0.44	0.25	0.33	0.06	0.14	0.19
3000	46.44	46.46	46.24	0.46	0.27	0.35	0.04	0.11	0.17
3300	49.27	49.09	48.70	0.49	0.31	0.39	0.02	0.10	0.17
3500	53.26	52.64	51.73	0.48	0.30	0.37	0.00	0.09	0.18
3700	64.37	61.41	58.87	0.47	0.32	0.37	0.01	0.10	0.20
3900	48.91	52.41	56.18	0.39	0.24	0.30	0.02	0.12	0.23
4000	41.97	45.29	48.32	0.25	0.13	0.22	0.03	0.13	0.24
4200	25.01	30.21	34.60	1.54	0.71	0.26	0.25	0.24	0.32
4500	22.61	18.46	16.45	0.67	1.44	1.47	0.51	1.43	2.45
4700	31.26	29.72	27.70	4.17	2.18	1.24	0.06	0.21	0.46
4900	26.43	28.83	30.62	1.03	1.53	2.98	0.10	0.19	0.38
5000	29.04	24.80	26.96	0.69	1.82	1.34	0.12	0.31	0.43
5300	49.51	56.61	48.60	0.47	0.21	0.08	0.02	0.17	0.40
5500	41.40	43.40	45.25	0.51	0.25	0.18	0.01	0.16	0.40
5700	38.59	39.42	40.25	0.58	0.29	0.24	0.02	0.18	0.43
5900	36.15	37.07	37.75	0.61	0.30	0.26	0.04	0.21	0.45
6000	35.21	36.25	36.59	0.50	0.20	0.14	0.08	0.23	0.47
6300	32.20	32.99	33.84	0.25	0.01	0.10	0.14	0.28	0.50
6500	29.64	30.83	31.93	0.11	0.28	0.37	0.32	0.38	0.55
6700	26.79	28.11	29.61	0.92	0.84	0.76	1.25	0.80	0.76
6900	37.68	29.66	27.83	2.57	2.29	1.87	2.79	2.90	1.82
7000	48.66	40.35	32.06	4.36	3.35	2.77	1.36	2.78	2.98
7300	34.83	38.12	42.39	8.71	11.99	9.96	0.54	0.73	1.10
7500	31.45	32.91	34.77	2.81	5.07	8.64	0.87	0.77	0.85
7700	28.90	30.45	31.52	0.80	1.86	3.30	1.17	1.44	1.17
7900	27.13	28.03	29.05	0.04	0.71	1.47	0.60	0.87	1.23
8000	26.62	27.25	28.07	0.16	0.40	1.02	0.53	0.70	0.92
8100	26.14	26.77	27.49	0.25	0.27	0.78	0.51	0.63	0.75
8200	25.70	26.30	27.24	0.40	0.11	0.51	0.54	0.62	0.69
8300	25.45	26.09	26.64	0.42	0.07	0.39	0.60	0.64	0.67
8400	25.05	25.68	26.30	0.55	0.04	0.21	0.68	0.69	0.71
8500	24.80	25.24	25.80	0.64	0.16	0.04	0.76	0.74	0.73


Typical Performance Data

FREQ.	GROUP DELAY		
(MHz)	(nsec)		
	@-55°C	@+25°C	@+125°C
10	0.96	0.98	1.00
13	0.96	0.99	1.01
16	0.97	0.99	1.01
19	0.98	0.99	1.01
20	0.99	1.00	1.01
40	1.00	1.01	1.01
60	1.01	1.01	1.02
80	1.02	1.02	1.02
100	1.04	1.03	1.03
120	1.05	1.04	1.03
140	1.06	1.05	1.04
160	1.07	1.06	1.05
180	1.09	1.08	1.07
200	1.11	1.10	1.09
220	1.13	1.12	1.11
240	1.16	1.15	1.13
260	1.19	1.18	1.16
280	1.23	1.21	1.20
300	1.27	1.25	1.24
320	1.33	1.30	1.28
340	1.38	1.36	1.33
360	1.45	1.42	1.39
380	1.52	1.49	1.46
400	1.61	1.57	1.53
420	1.70	1.65	1.61
440	1.79	1.74	1.70
460	1.90	1.84	1.79
480	2.01	1.94	1.88
490	2.13	2.05	1.98
500	2.26	2.17	2.09
510	2.41	2.30	2.21
520	2.57	2.44	2.33
530	2.74	2.60	2.48
540	2.94	2.77	2.63
550	3.15	2.96	2.80
560	3.37	3.16	2.97
570	3.60	3.36	3.16
580	3.81	3.57	3.35
590	4.02	3.77	3.54
600	4.21	3.96	3.72
620	4.62	4.49	4.30


Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L
GE0805C-2	.079 (2.00)	.049 (1.25)	.037 (0.95)	.014 (0.35)	.012 (0.30)	.012 (0.30)	.026 (0.65)	.025 (0.63)	.134 (3.40)	.110 (2.80)	.014 (0.35)

CASE #	M	WT. GRAM
GE0805C-2	.039 (1.00)	.008

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Open style, ceramic base.
2. Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate over Nickel plate. All models, no (+) suffix.
3. Pad tolerance to be non-cumulative. Minimum spacing between each pad is .004 (0.1).



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F114

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

Applicable Case Styles	
GE0805C	JC0603C
GE0805C-1	JC0603C-4
GE0805C-1AP	JC0603C-6
GE0805C-7	
GE0805C-9	
GE0805C-10	
GE0805C-11	
GE0805C-12	




ILLUSTRATION 2

Applicable Case Styles	
GE0805C-2	JC0603C-1
GE0805C-3	JC0603C-2
GE0805C-4	JC0603C-3
GE0805C-5	JC0603C-5
GE0805C-6	JC0603C-7
GE0805C-8	JV1210C-1
GE0805C-15	

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	4000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M148457	NEW RELEASE	10/14/14	GF	MY

SUGGESTED MOUNTING CONFIGURATION
FOR GE0805C-4 CASE STYLE, "08FL07" PIN CODE

NOTES:

1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:
 2 PL DECIMALS ±
 3 PL DECIMALS ± .005
 ANGLES ±
 FRACTIONS ±

INITIALS

DRAWN

GF

DATE

10/01/14

CHECKED

IL

10/14/14

APPROVED

MY

10/14/14



Mini-Circuits®

 13 Neptune Avenue
 Brooklyn NY 11235

PL, 08FL07, GE0805C-4, TB-799+

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

 Mini-Circuits®

ASHEETA1.DWG REV:A DATE:01/12/95

 SIZE
 A

 CODE IDENT
 15542

DRAWING NO:

98-PL-429

REV:

OR


FILE: 98PL429

SCALE: 15:1

SHEET:

1 OF 1

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.010 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, Except +100°C