

RACK-MOUNTED

SMA Adapter Patch Panel

ZT-346

Mini-Circuits

50Ω DC to 18 GHz

THE BIG DEAL

- Convenient panel-mounted design
- Excellent VSWR
- Flat frequency response



CASE STYLE: YF3183

APPLICATIONS

- Production test set-ups
- Simplification of cable runs
- Interconnection of RF cables & equipment

RoHS Compliant

See our website for RoHS Compliance methodologies and qualifications

PRODUCT OVERVIEW

Mini-Circuits panel-mounted structures provide clean, organized management of cable runs and connections in complex, high-volume test setups. Multiple connector adapters, power splitters, directional couplers and other essential RF components and test accessories can be integrated efficiently within the test system. Custom configurations are available upon request.

ZT-346 is a 1U height patch panel incorporating 12 high quality connector adaptors, with SMA female connectors on the front and rear of the panel.

ELECTRICAL SPECIFICATIONS AT 25°C


Parameter	Frequency (GHz)	Min.	Typ.	Max.	Unit
Frequency	-	DC	-	18	GHz
Insertion Loss	DC – 18	-	0.1	-	dB
VSWR	DC – 18	-	-	1.15	:1

MECHANICAL & ENVIRONMENTAL SPECIFICATIONS

Dimensions	19" (W) x 1U (H)			
Case Style	YF3183			
Case Material	Aluminum (with protective coating to prevent corrosion)			
RF Connectors	Face	Connector	Quantity	Port Labels
	Front	SMA female	12	01-12
	Rear	SMA female	12	None
Panel Marking	Front Panel	Rear Panel		
	ZT-346	- CE / EAC / UKCA - Serial number / date code / model name		
Panel Items	Carry handles			
Temperature	Operating: 0 to +50 °C			

REV. A
ECO-013880
ZT-346
MCL NY
220623





RACK-MOUNTED

SMA Adapter Patch Panel



ZT-346

Mini-Circuits

50Ω DC to 18 GHz

TYPICAL PERFORMANCE CURVES

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	
		SMA-FEM	SMA-FEM
10	0.01	1.00	1.00
50	0.00	1.00	1.00
100	0.00	1.00	1.00
500	0.01	1.01	1.01
1000	0.03	1.02	1.02
1500	0.03	1.02	1.02
2000	0.04	1.03	1.03
2500	0.04	1.03	1.03
3000	0.04	1.03	1.04
4000	0.04	1.03	1.03
5000	0.04	1.02	1.02
6000	0.04	1.02	1.02
9000	0.07	1.09	1.09
10000	0.08	1.11	1.11
12000	0.09	1.10	1.09
13000	0.08	1.09	1.08
14000	0.08	1.04	1.04
15000	0.10	1.03	1.03
17000	0.12	1.09	1.09
18000	0.11	1.12	1.13



Mini-Circuits



RACK-MOUNTED


SMA Adapter Patch Panel

ZT-346

Mini-Circuits

50Ω DC to 18 GHz

OUTLINE DRAWING



OUTLINE DIMENSIONS (Inch/mm)

A	B	C	D	E	F	G	H	J	K	L	wt
1.73	19.00	0.40	0.13	15.60	1.250	18.340	0.87	1.98	1.35	8.29	grams
43.9	482.6	10.2	3.30	396.24	31.8	465.8	22.10	50.3	34.3	210.6	240





Mini-Circuits®

RACK-MOUNTED

SMA Adapter Patch Panel

ZT-346

50Ω DC to 18 GHz




ORDERING INFORMATION

To learn more, click here: [ZT-346](#)

Model	Description
ZT-346	12 x SMA female to female patch panel

Included Accessories	Part No.	Description
	HT-4-SMA	SMA Cable Wrench (4 in)





CASE #	A	B	C	D	E	F	G	H	J	K	L	WT, GRAMS
YF3183	1.73 (43.9)	19.00 (482.6)	.40 (10.2)	.13 (3.3)	15.60 (396.2)	1.250 (31.75)	18.340 (465.84)	.87 (22.1)	1.98 (50.3)	1.35 (34.3)	8.29 (210.6)	240

Dimensions are in inches (mm) . Tolerances: 2 Pl. $\pm .1$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Finish: Clear chemical conversion coating



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



Environmental Specifications ENV56

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-0° to 40° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-15° to 85° C Ambient Environment	Individual Model Data Sheet
Operating and Storage Humidity	5% to 85% RH (non-condensing)	Ambient
Bench Handling Test	Bench Top Tip 45° & Drop	MIL-PRF-28800F
Transit Drop Test	Free Fall Drop, 20 cm (7.9 inches)	MIL-PRF-28800F Class 3