


Outline Dimensions



GM1132 SERIES

SMA FEMALE (CONN-1)

N MALE (CONN-2)

CASE STYLE #	A		B	C	D	E	T		WEIGHT GRAMS
	FEET	METERS					FEET	METERS	
GM1132-1	1	.30	.51 (12.95)	--	.88 (22.35)	.750 (19.05)	.06	.02	79
GM1132-2	2	.61					.06	.02	98
GM1132-3	3	.91					.09	.03	118
GM1132-4	4	1.22					.12	.04	137
GM1132-5	5	1.52					.15	.05	157
GM1132-6	6	1.83					.18	.05	176

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. Flexible Coaxial Cable.