


Outline Dimensions



SG2638 SERIES
 SMA MALE (CONN-1)
 N MALE (CONN-2)

| CASE STYLE # | A | | B | C1 | C2 | D | E1 | E2 | F | T | | WEIGHT GRAMS |
|--------------|------|-------|---------------|----------------|----|---------------|----------------|---------------|--------------------------|------|------|--------------|
| | INCH | MM | | | | | | | | INCH | MM | |
| SG2638-6 | 6 | 152.4 | .36 (9.14) | .313 (7.95) | - | .88 (22.0) | .750 (19.0) | .375 (9.5) | .163±.006 (4.14±0.15) | 0.05 | 1.27 | 43.74 |
| SG2638-12 | 12 | 304.8 | | | | | | | | 0.10 | 2.54 | 50.38 |
| SG2638-24 | 24 | 609.6 | | | | | | | | 0.15 | 3.81 | 63.67 |

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. 141 Flexible Coaxial Cable.
2. "A" Represents Length of Cable.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/MICROWAVE COMPONENTS