


Outline Dimensions



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N
GGG126	2.25 (57.15)	1.38 (35.05)	1.24 (31.50)	.50 (12.70)	.150 (3.81)	3.100 (78.74)	.138 (3.51)	1.238 (31.45)	3.25 (82.55)	.12 (3.05)	.80 (20.32)	.69 (17.53)	--

CASE #.	P	Q	R	S	T	WT, GRAM
GGG126	.60 (15.24)	1.200 (30.48)	.52 (13.21)	.82 (20.83)	.150 (3.81)	80.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.