

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMP-FEMALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMP-FEMALE 2 RETURN LOSS (dB)
100	0.03	41.1	40.5
200	0.04	35.0	34.5
300	0.06	31.7	31.4
400	0.07	29.6	29.4
500	0.08	28.4	28.2
600	0.09	27.9	27.8
700	0.11	27.9	27.6
800	0.10	28.5	28.4
900	0.11	29.8	29.5
1000	0.12	31.9	31.7
1100	0.13	35.6	35.0
1200	0.13	42.3	40.0
1300	0.13	44.7	41.0
1400	0.13	36.9	35.8
1500	0.14	32.8	32.3
1600	0.15	30.4	30.1
1800	0.17	28.4	28.1
2000	0.17	28.5	28.1
2500	0.17	35.5	30.8
3000	0.20	31.7	30.8
3500	0.21	31.2	29.0
4000	0.22	31.3	26.2
4500	0.26	34.9	33.3
5000	0.27	32.3	30.1
5500	0.29	33.5	28.8
6000	0.28	40.3	47.6
6500	0.31	29.3	30.8
7000	0.31	30.4	36.9
7500	0.31	35.1	35.4
8000	0.32	31.9	51.3
8500	0.33	36.5	35.4
9000	0.34	37.7	44.1
9500	0.34	39.3	27.1
10000	0.37	32.1	26.8
10500	0.36	31.1	34.3
11000	0.37	30.8	26.9
11500	0.45	23.9	28.7
12000	0.36	24.4	24.9
12500	0.48	26.2	27.3
13000	0.28	22.7	23.0
13500	0.44	22.5	21.1
14000	0.52	23.5	36.7
14500	0.43	23.8	21.7
15000	0.36	26.4	23.9
15500	0.49	38.1	26.8
16000	0.46	31.4	21.1
16500	0.45	36.8	35.2
17000	0.50	24.9	21.0
17500	0.44	24.0	27.9
18000	0.48	21.4	20.7