


Outline Dimensions

UU2061-1



CASE#	A	B	C	D	E	F	G	H	J	K	L
UU2061-1	8.50 (215.90)	9.50 (241.30)	.50 (12.70)	.15 (3.81)	8.200 (208.28)	.75 (19.05)	8.000 (203.2)	.136 (3.45)	4.25 (107.95)	.205 (5.21)	.63 (15.88)

CASE#	M	N	P	Q	R	S	WT. GRAMS
UU2061-1	1.88 (47.63)	3.13 (79.38)	4.88 (123.83)	6.13 (155.58)	7.38 (187.33)	.500 (12.70)	1.190

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

1. Case material: Aluminum alloy.
2. Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
3. Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS