

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.11	40.8	41.5
200.0	0.15	45.2	45.1
300.0	0.19	45.4	43.2
400.0	0.23	41.7	43.4
600.0	0.28	41.5	42.6
800.0	0.33	39.6	39.9
900.0	0.35	44.0	41.0
1000.0	0.37	41.6	39.5
1100.0	0.39	38.3	40.4
1250.0	0.42	37.7	38.7
1500.0	0.46	36.8	36.9
1750.0	0.50	36.7	37.4
2000.0	0.53	36.1	35.8
2001.0	0.53	36.2	35.9
2250.0	0.56	36.5	36.0
2500.0	0.60	34.5	35.6
2750.0	0.63	41.3	46.5
3250.0	0.69	38.9	38.4
3500.0	0.71	36.6	37.2
3750.0	0.74	31.5	32.3
4000.0	0.77	29.1	29.8
4250.0	0.80	29.5	30.1
4500.0	0.83	27.6	28.6
5000.0	0.87	31.2	32.6
5500.0	0.91	35.6	40.0
6000.0	0.96	39.5	50.4
6500.0	1.00	37.5	39.1
7000.0	1.04	30.5	35.1
7500.0	1.08	39.9	52.4
8000.0	1.11	40.0	51.9
8500.0	1.15	29.9	31.1
9000.0	1.19	30.1	30.4
9500.0	1.23	29.4	29.6
10000.0	1.27	48.9	37.1
10500.0	1.31	41.9	33.9
11000.0	1.35	30.8	31.9
11500.0	1.42	24.7	24.3
12000.0	1.45	24.1	24.1
12500.0	1.47	29.8	28.1
13000.0	1.51	37.7	34.9
13500.0	1.56	25.6	25.3
14000.0	1.60	21.8	21.6
14500.0	1.63	27.5	25.7
15000.0	1.65	28.8	30.9
15500.0	1.71	29.7	27.4
16000.0	1.75	26.1	24.3
16500.0	1.79	24.4	23.7
17000.0	1.81	27.9	27.6
17500.0	1.84	31.6	33.3
18000.0	1.89	27.9	27.9