

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.03	46.4	47.4
200.0	0.04	44.0	44.4
300.0	0.05	42.9	43.3
400.0	0.07	43.6	43.4
500.0	0.07	45.8	44.4
600.0	0.08	50.0	45.8
700.0	0.09	54.2	46.9
800.0	0.09	52.2	46.9
900.0	0.10	46.7	45.4
1000.0	0.10	43.2	43.7
1100.0	0.11	41.6	42.4
1250.0	0.11	40.6	41.6
1500.0	0.12	44.2	44.2
1750.0	0.13	48.4	45.6
2000.0	0.14	38.1	38.1
2250.0	0.15	33.6	33.7
2500.0	0.16	34.1	34.3
2750.0	0.16	43.2	40.5
3000.0	0.17	43.2	40.5
3250.0	0.18	32.7	33.1
3500.0	0.18	31.2	31.5
3750.0	0.18	34.0	33.5
4000.0	0.19	39.0	38.5
4250.0	0.20	36.7	37.4
4500.0	0.21	31.0	31.7
5000.0	0.21	31.2	32.3
5500.0	0.22	36.0	39.2
6000.0	0.23	30.8	33.3
6500.0	0.23	37.9	41.4
7000.0	0.25	31.7	37.0
7500.0	0.25	39.5	48.4
8000.0	0.27	33.2	37.8
8500.0	0.27	37.0	44.8
9000.0	0.27	36.9	40.7
9500.0	0.28	28.8	30.8
10000.0	0.29	43.5	41.3
10500.0	0.34	28.5	30.5
11000.0	0.32	32.6	32.9
11500.0	0.32	28.9	29.7
12000.0	0.34	24.6	24.8
12500.0	0.31	26.4	27.6
13000.0	0.36	21.7	22.0
13500.0	0.34	28.6	28.2
14000.0	0.37	25.0	25.3
14500.0	0.38	24.3	24.5
15000.0	0.36	25.9	26.8
15500.0	0.41	21.6	21.7
16000.0	0.37	27.2	26.3
16500.0	0.44	21.8	22.1
17000.0	0.41	28.2	27.4
17500.0	0.41	26.6	26.4
18000.0	0.41	23.3	24.3