

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMP-FEMALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMP-FEMALE 2 RETURN LOSS (dB)
100	0.03	40.5	40.1
200	0.05	34.4	34.0
300	0.06	31.2	31.0
400	0.07	29.1	29.0
500	0.08	28.0	27.8
600	0.09	27.5	27.4
700	0.11	27.6	27.4
800	0.10	28.3	28.2
900	0.12	29.7	29.5
1000	0.13	32.0	31.8
1100	0.13	36.1	35.6
1200	0.13	44.1	41.4
1300	0.14	42.4	39.8
1400	0.14	35.2	34.2
1500	0.14	31.5	31.0
1600	0.16	29.2	28.8
1800	0.18	27.2	27.0
2000	0.17	27.2	26.9
2500	0.17	34.6	31.3
3000	0.20	38.8	36.1
3500	0.21	33.3	29.7
4000	0.22	32.6	26.4
4500	0.26	39.8	36.3
5000	0.27	32.5	29.2
5500	0.29	29.8	27.0
6000	0.29	34.7	33.2
6500	0.31	30.4	27.5
7000	0.30	28.3	27.9
7500	0.33	34.0	34.1
8000	0.33	35.8	43.3
8500	0.34	28.6	38.5
9000	0.34	29.5	32.1
9500	0.36	31.9	33.1
10000	0.39	21.6	33.8
10500	0.30	22.9	24.1
11000	0.37	25.3	23.4
11500	0.47	20.2	32.7
12000	0.34	23.8	24.8
12500	0.51	20.0	23.2
13000	0.29	18.9	34.8
13500	0.43	24.1	23.3
14000	0.57	20.3	24.9
14500	0.41	22.8	31.7
15000	0.37	27.4	23.5
15500	0.61	24.7	35.8
16000	0.49	33.5	25.1
16500	0.51	28.8	26.9
17000	0.57	28.0	29.7
17500	0.48	18.9	26.2
18000	0.49	25.5	28.0