

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	SMA-FEMALE BULKHEAD RETURN LOSS (dB)
100.0	0.03	48.1	48.0
500.0	0.07	48.2	44.5
1000.0	0.10	61.8	46.6
1100.0	0.11	58.5	44.1
1200.0	0.11	51.8	42.8
1300.0	0.12	48.1	43.1
1400.0	0.12	45.0	43.4
1500.0	0.13	42.5	43.8
1600.0	0.13	41.7	43.5
1700.0	0.14	41.3	43.4
1800.0	0.14	42.0	43.1
1900.0	0.14	44.7	43.6
2000.0	0.14	49.8	45.3
2400.0	0.16	37.4	39.6
3000.0	0.18	57.1	45.4
4000.0	0.21	42.0	51.3
5000.0	0.23	35.7	36.5
5500.0	0.26	24.7	26.5
6000.0	0.26	28.4	29.7
6500.0	0.30	23.2	25.2
7000.0	0.29	25.7	25.3
7500.0	0.32	23.6	27.0
8000.0	0.33	21.1	22.7
8500.0	0.33	27.1	27.0
9000.0	0.36	20.7	21.1
9500.0	0.34	33.7	29.9
10000.0	0.40	19.3	19.4
10500.0	0.36	31.5	28.2
11000.0	0.40	20.1	20.5
11500.0	0.37	29.8	26.1
12000.0	0.43	22.5	22.8
12500.0	0.44	21.9	22.8
13000.0	0.40	28.8	25.2
13500.0	0.45	21.8	22.3
14000.0	0.42	36.0	23.5
14500.0	0.49	21.0	22.5
15000.0	0.41	42.3	25.5
15500.0	0.46	25.5	24.0
16000.0	0.44	31.0	23.7
16500.0	0.47	23.4	24.4
17000.0	0.48	28.4	27.2
17500.0	0.47	24.4	21.5
18000.0	0.48	22.7	30.2